

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P739983

Luminaire Tested: LD4D05D010-EU4DR200210IC9050-4LBDP1LI

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P739983
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-36)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D05D010-EU4DR200210IC9050-4LBDP1LI
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 20° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 758.0 lumens
Efficiency: N/A
Efficacy: 101.1 lumens/watt
Spacing Criteria (0/90/45): 0.34 / 0.34 / 0.36
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 7.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P739983

CATALOG NUMBER: LD4D05D010-EU4DR200210IC9050-4LBDP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P739983

CATALOG NUMBER: LD4D05D010-EU4DR200210IC9050-4LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100															
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97	97	98	98	97															
2	111	108	105	102	109	106	104	101	103	101	99	100	99	97	98	96	95	94	94	98	96	95															
3	108	103	100	97	106	102	99	96	100	97	95	97	95	93	95	93	92	91	91	98	93	92															
4	105	99	96	93	103	98	95	92	96	93	91	95	92	90	93	91	89	88	88	93	91	89															
5	102	96	92	89	100	95	91	89	94	90	88	92	89	87	91	88	86	85	85	91	88	86															
6	99	93	89	86	98	92	88	86	91	87	85	90	87	84	88	86	84	83	83	88	86	84															
7	96	90	86	83	95	89	86	83	88	85	82	87	84	82	86	84	82	81	81	86	84	82															
8	94	87	83	81	93	87	83	80	86	83	80	85	82	80	84	82	80	79	79	84	82	80															
9	91	85	81	78	91	85	81	78	84	80	78	83	80	78	82	80	78	77	77	82	80	78															
10	89	83	79	76	88	82	79	76	82	78	76	81	78	76	81	78	76	75	75	81	78	76															

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	471351
5°	425244
10°	238668
15°	121316
20°	51369
25°	23713
30°	12553
35°	6763
40°	3623
45°	2132
50°	1241
55°	667
60°	415
65°	310
70°	128
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2132 cd/sqm



TEST NUMBER: P739983

CATALOG NUMBER: LD4D05D010-EU4DR200210IC9050-4LBDP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	307.2	40.5
10°-20°	302.4	39.9
20°-30°	98.8	13.0
30°-40°	33.6	4.4
40°-50°	11.3	1.5
50°-60°	3.4	0.5
60°-70°	1.1	0.2
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	708.4	93.5
0°-40°	742.0	97.9
0°-60°	756.8	99.8
0°-90°	758.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	758.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4314	
5°	3877	307
15°	1072	302
25°	197	99
35°	51	34
45°	14	11
55°	4	3
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P739983

CATALOG NUMBER: LD4D05D010-EU4DR200210IC9050-4LBDP1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	4314.0
0.5°	4314.0
1°	4308.6
1.5°	4297.9
2°	4278.3
2.5°	4252.2
3°	4215.3
3.5°	4163.8
4°	4087.4
4.5°	3994.4
5°	3877.2
5.5°	3723.2
6°	3565.3
6.5°	3384.4
7°	3207.3
7.5°	2999.8
8°	2814.7
8.5°	2628.4
9°	2456.3
9.5°	2298.4
10°	2151.2
12.5°	1544.7
15°	1072.5
17.5°	700.7
20°	441.8
22.5°	286.2
25°	196.7
27.5°	138.3
30°	99.5
32.5°	71.5
35°	50.7
37.5°	35.3
40°	25.4
42.5°	18.4
45°	13.8
47.5°	10.8
50°	7.3
52.5°	4.6
55°	3.5
57.5°	2.7
60°	1.9
62.5°	1.5
65°	1.2



TEST NUMBER: P739983

CATALOG NUMBER: LD4D05D010-EU4DR200210IC9050-4LBDP1LI

CANDELA DISTRIBUTION (continued):

	0°
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





67.5°		0.8
70°		0.4

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)