

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P748193

Luminaire Tested: LD4D40BD010-EU4DR7040509035-4LBDP1LI

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P748193  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D40BD010-EU4DR7040509035-4LBDP1LI  
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 70° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4029.2 lumens  
Efficiency: N/A  
Efficacy: 114.5 lumens/watt  
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 35.2  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight

TEST NUMBER: P748193

CATALOG NUMBER: LD4D40BD010-EU4DR7040509035-4LBDP1LI

### Luminous Intensity Polar Plot





TEST NUMBER: P748193  
 CATALOG NUMBER: LD4D40BD010-EU4DR7040509035-4LBDP1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20		
RC	80				70				50				30				10		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30
RCR																			
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91	
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83	
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76	
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70	
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65	
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61	
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57	
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53	
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50	
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48	

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	494951
5°	480248
10°	466862
15°	460729
20°	430233
25°	323210
30°	228482
35°	80937
40°	42561
45°	45320
50°	46931
55°	47813
60°	48118
65°	47105
70°	44436
75°	41160
80°	36557
85°	29711

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 57.5°  
 Luminance: 48133 cd/sqm



TEST NUMBER: P748193

CATALOG NUMBER: LD4D40BD010-EU4DR7040509035-4LBDP1LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	413.0	10.3
10°-20°	1132.8	28.1
20°-30°	1247.7	31.0
30°-40°	476.7	11.8
40°-50°	225.1	5.6
50°-60°	223.8	5.6
60°-70°	179.2	4.4
70°-80°	102.9	2.6
80°-90°	28.0	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2793.5	69.3
0°-40°	3270.2	81.2
0°-60°	3719.1	92.3
0°-90°	4029.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4029.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4530	
5°	4379	413
15°	4073	1133
25°	2681	1248
35°	607	477
45°	293	225
55°	251	224
65°	182	179
75°	98	103
85°	24	28
90°	0	



TEST NUMBER: P748193

CATALOG NUMBER: LD4D40BD010-EU4DR7040509035-4LBDP1LI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	4530.0
2.5°	4482.7
5°	4378.7
7.5°	4291.9
10°	4208.0
12.5°	4137.0
15°	4073.1
17.5°	3918.9
20°	3700.2
22.5°	3228.2
25°	2681.0
27.5°	2333.8
30°	1811.0
32.5°	1169.8
35°	606.8
37.5°	327.8
40°	298.4
42.5°	296.2
45°	293.3
47.5°	286.9
50°	276.1
52.5°	263.9
55°	251.0
57.5°	236.7
60°	220.2
62.5°	201.5
65°	182.2
67.5°	160.7
70°	139.1
72.5°	117.6
75°	97.5
77.5°	76.7
80°	58.1
82.5°	40.9
85°	23.7
87.5°	9.3
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)