

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P749246

Luminaire Tested: LD4D50D010-EU4DR4040509024-4LBDP1LI

Issue Date: 1/30/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P749246  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-28)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 1/30/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D50D010-EU4DR4040509024-4LBDP1LI  
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 40° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4545.6 lumens  
Efficiency: N/A  
Efficacy: 96.7 lumens/watt  
Spacing Criteria (0/90/45): 0.68 / 0.68 / 0.6  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct


Input Watts (W): 47  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



Downlight

TEST NUMBER: P749246  
CATALOG NUMBER: LD4D50D010-EU4DR4040509024-4LBDP1LI

### Luminous Intensity Polar Plot





TEST NUMBER: P749246

CATALOG NUMBER: LD4D50D010-EU4DR4040509024-4LBDP1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									20								
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR	0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	99	98	97	96	95	94	93	92																
	1	115	112	110	108	112	110	108	107	106	105	103	103	101	100	99	98	97	96	95	94	93	92	91	90	89	88	87	86																
	2	110	106	103	100	108	105	102	99	102	99	97	99	97	95	96	95	93	92	91	90	89	88	87	86	85	84	83	82																
	3	106	101	97	94	104	100	96	93	97	94	92	95	93	90	93	91	89	88	87	86	85	84	83	82	81	80	79	78																
	4	102	97	92	89	101	95	91	88	93	90	87	92	89	86	90	87	85	84	83	82	81	80	79	78	77	76	75	74																
	5	99	92	88	84	97	91	87	84	90	86	83	88	85	83	87	84	82	81	80	79	78	77	76	75	74	73	72	71																
	6	95	88	84	80	94	88	83	80	86	82	80	85	82	79	84	81	79	78	77	76	75	74	73	72	71	70	69	68																
	7	92	85	80	77	91	84	80	77	83	79	76	82	79	76	81	78	76	75	74	73	72	71	70	69	68	67	66	65																
	8	89	82	77	74	88	81	77	74	80	76	73	79	76	73	78	75	73	72	71	70	69	68	67	66	65	64	63	62																
	9	86	79	74	71	85	78	74	71	77	73	71	76	73	70	76	72	70	69	68	67	66	65	64	63	62	61	60	59																
	10	83	76	71	68	82	75	71	68	75	71	68	74	70	68	73	70	68	67	66	65	64	63	62	61	60	59	58	57																

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1156328
5°	1150710
10°	1087673
15°	924659
20°	630222
25°	262957
30°	82675
35°	38428
40°	21252
45°	9750
50°	4725
55°	2591
60°	1355
65°	491
70°	192
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 9750 cd/sqm



TEST NUMBER: P749246

CATALOG NUMBER: LD4D50D010-EU4DR4040509024-4LBDP1LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	979.7	21.6
10°-20°	2194.7	48.3
20°-30°	1098.6	24.2
30°-40°	201.4	4.4
40°-50°	55.6	1.2
50°-60°	13.1	0.3
60°-70°	2.5	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4273.0	94.0
0°-40°	4474.3	98.4
0°-60°	4543.0	99.9
0°-90°	4545.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4545.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	10583	
5°	10492	980
15°	8174	2195
25°	2181	1099
35°	288	201
45°	63	56
55°	14	13
65°	2	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P749246

CATALOG NUMBER: LD4D50D010-EU4DR4040509024-4LBDP1LI

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	10583.2
2.5°	10567.8
5°	10491.7
7.5°	10249.4
10°	9803.6
12.5°	9108.7
15°	8174.5
17.5°	6959.7
20°	5420.2
22.5°	3695.3
25°	2181.2
27.5°	1153.0
30°	655.3
32.5°	423.5
35°	288.1
37.5°	205.9
40°	149.0
42.5°	102.0
45°	63.1
47.5°	40.2
50°	27.8
52.5°	19.8
55°	13.6
57.5°	8.7
60°	6.2
62.5°	3.7
65°	1.9
67.5°	1.2
70°	0.6
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)