

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P749714

Luminaire Tested: LD4D50D010-EU4DR7040509024-4LBDP1LI

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P749714
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D50D010-EU4DR7040509024-4LBDP1LI
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4395.2 lumens
Efficiency: N/A
Efficacy: 93.5 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 47
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P749714
CATALOG NUMBER: LD4D50D010-EU4DR7040509024-4LBDP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P749714

CATALOG NUMBER: LD4D50D010-EU4DR7040509024-4LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	539912
5°	523867
10°	509266
15°	502582
20°	469312
25°	352566
30°	249236
35°	88286
40°	46426
45°	49446
50°	51198
55°	52156
60°	52489
65°	51371
70°	48494
75°	44917
80°	39892
85°	32344

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 52505 cd/sqm



TEST NUMBER: P749714

CATALOG NUMBER: LD4D50D010-EU4DR7040509024-4LBDP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	450.5	10.3
10°-20°	1235.8	28.1
20°-30°	1361.0	31.0
30°-40°	520.0	11.8
40°-50°	245.5	5.6
50°-60°	244.1	5.6
60°-70°	195.4	4.4
70°-80°	112.3	2.6
80°-90°	30.5	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3047.3	69.3
0°-40°	3567.3	81.2
0°-60°	4056.9	92.3
0°-90°	4395.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4395.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4942	
5°	4776	451
15°	4443	1236
25°	2924	1361
35°	662	520
45°	320	246
55°	274	244
65°	199	195
75°	106	112
85°	26	31
90°	0	



TEST NUMBER: P749714

CATALOG NUMBER: LD4D50D010-EU4DR7040509024-4LBDP1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	4941.5
2.5°	4889.9
5°	4776.4
7.5°	4681.7
10°	4590.2
12.5°	4512.8
15°	4443.1
17.5°	4274.9
20°	4036.3
22.5°	3521.5
25°	2924.5
27.5°	2545.9
30°	1975.5
32.5°	1276.1
35°	661.9
37.5°	357.5
40°	325.5
42.5°	323.1
45°	320.0
47.5°	313.0
50°	301.2
52.5°	287.9
55°	273.8
57.5°	258.2
60°	240.2
62.5°	219.8
65°	198.7
67.5°	175.3
70°	151.8
72.5°	128.3
75°	106.4
77.5°	83.7
80°	63.4
82.5°	44.6
85°	25.8
87.5°	10.2
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)