

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P749569

Luminaire Tested: LD4D50D010-EU4DR6040509027-4LBDP1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P749569
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D50D010-EU4DR6040509027-4LBDP1B
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3709.7 lumens
Efficiency: N/A
Efficacy: 78.9 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 47
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P749569
CATALOG NUMBER: LD4D50D010-EU4DR6040509027-4LBDP1B

Luminous Intensity Polar Plot





TEST NUMBER: P749569

CATALOG NUMBER: LD4D50D010-EU4DR6040509027-4LBDP1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93			93																
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86			86																
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80			80																
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75			75																
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70			70																
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66			66																
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62			62																
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59			59																
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55			55																
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53			53																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	481370
5°	493212
10°	499169
15°	475524
20°	419268
25°	339112
30°	229378
35°	114949
40°	18642
45°	18249
50°	18613
55°	18897
60°	19427
65°	19855
70°	20317
75°	20559
80°	19820
85°	16548

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 20559 cd/sqm



TEST NUMBER: P749569

CATALOG NUMBER: LD4D50D010-EU4DR6040509027-4LBDP1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	429.8	11.6
10°-20°	1162.8	31.3
20°-30°	1251.1	33.7
30°-40°	543.8	14.7
40°-50°	91.3	2.5
50°-60°	88.8	2.4
60°-70°	75.9	2.0
70°-80°	50.8	1.4
80°-90°	15.2	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2843.7	76.7
0°-40°	3387.5	91.3
0°-60°	3567.7	96.2
0°-90°	3709.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3709.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4406	
5°	4497	430
15°	4204	1163
25°	2813	1251
35°	862	544
45°	118	91
55°	99	89
65°	77	76
75°	49	51
85°	13	15
90°	0	



TEST NUMBER: P749569

CATALOG NUMBER: LD4D50D010-EU4DR6040509027-4LBDP1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	4405.7
2.5°	4529.5
5°	4496.9
7.5°	4507.2
10°	4499.2
12.5°	4406.3
15°	4203.9
17.5°	3932.1
20°	3605.9
22.5°	3256.7
25°	2812.9
27.5°	2249.9
30°	1818.1
32.5°	1401.3
35°	861.8
37.5°	368.7
40°	130.7
42.5°	120.4
45°	118.1
47.5°	114.1
50°	109.5
52.5°	104.4
55°	99.2
57.5°	94.0
60°	88.9
62.5°	83.1
65°	76.8
67.5°	70.5
70°	63.6
72.5°	56.2
75°	48.7
77.5°	40.1
80°	31.5
82.5°	22.4
85°	13.2
87.5°	4.6
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)