

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P749653

Luminaire Tested: LD4D50D010-EU4DR6540509027-4LBS1LI

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P749653  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D50D010-EU4DR6540509027-4LBS1LI  
Description: 4 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 65° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4549.4 lumens  
Efficiency: N/A  
Efficacy: 96.8 lumens/watt  
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96  
Luminous Opening: Circular (Dia: 0.48' x H: 0')  
CIE Type: Direct


Input Watts (W): 47  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



Downlight

TEST NUMBER: P749653  
CATALOG NUMBER: LD4D50D010-EU4DR6540509027-4LBS1LI

### Luminous Intensity Polar Plot





TEST NUMBER: P749653

CATALOG NUMBER: LD4D50D010-EU4DR6540509027-4LBS1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93			93
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85			85
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78			78
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72			72
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66			66
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61			61
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56			56
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52			52
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49			49
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46			46

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	241255
5°	240646
10°	240440
15°	233029
20°	212144
25°	184870
30°	153761
35°	121834
40°	87929
45°	55554
50°	28957
55°	15386
60°	8083
65°	4450
70°	1861
75°	2053
80°	1413
85°	1206

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 55554 cd/sqm



TEST NUMBER: P749653

CATALOG NUMBER: LD4D50D010-EU4DR6540509027-4LBS1LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	390.6	8.6
10°-20°	1069.7	23.5
20°-30°	1307.6	28.7
30°-40°	1060.9	23.3
40°-50°	528.7	11.6
50°-60°	147.4	3.2
60°-70°	33.5	0.7
70°-80°	8.7	0.2
80°-90°	2.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2767.9	60.8
0°-40°	3828.9	84.2
0°-60°	4505.0	99.0
0°-90°	4549.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4549.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4131	
5°	4105	391
15°	3854	1070
25°	2869	1308
35°	1709	1061
45°	673	529
55°	151	147
65°	32	34
75°	9	9
85°	2	2
90°	0	



TEST NUMBER: P749653

CATALOG NUMBER: LD4D50D010-EU4DR6540509027-4LBS1LI

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	4130.8
2.5°	4127.8
5°	4104.7
7.5°	4091.3
10°	4054.3
12.5°	3979.0
15°	3854.0
17.5°	3658.5
20°	3413.3
22.5°	3148.6
25°	2868.8
27.5°	2569.5
30°	2280.0
32.5°	1994.1
35°	1708.8
37.5°	1424.1
40°	1153.3
42.5°	899.6
45°	672.6
47.5°	468.6
50°	318.7
52.5°	219.7
55°	151.1
57.5°	102.0
60°	69.2
62.5°	48.0
65°	32.2
67.5°	16.4
70°	10.9
72.5°	10.3
75°	9.1
77.5°	6.1
80°	4.2
82.5°	3.0
85°	1.8
87.5°	1.2
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)