

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P748127

Luminaire Tested: LD4D40BD010-EU4DR6540509040-4LBDP1H

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P748127  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D40BD010-EU4DR6540509040-4LBDP1H  
Description: 4 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 65° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3486.9 lumens  
Efficiency: N/A  
Efficacy: 99.1 lumens/watt  
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct


Input Watts (W): 35.2  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



Downlight

TEST NUMBER: P748127  
CATALOG NUMBER: LD4D40BD010-EU4DR6540509040-4LBDP1H

### Luminous Intensity Polar Plot





TEST NUMBER: P748127

CATALOG NUMBER: LD4D40BD010-EU4DR6540509040-4LBDP1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93																			
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87																			
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80																			
4	97	89	84	79	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	83	78	73	90	83	77	73	81	76	72	79	75	72	77	74	71	69																			
6	87	78	72	68	86	77	72	68	76	71	67	74	70	67	73	69	66	65																			
7	83	73	67	63	81	73	67	63	71	66	62	70	66	62	69	65	62	60																			
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	57																			
9	75	65	59	55	74	65	59	55	64	58	55	63	58	55	62	58	54	53																			
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	375092
5°	375406
10°	388623
15°	389263
20°	358388
25°	305368
30°	233768
35°	165155
40°	97487
45°	39572
50°	14346
55°	8001
60°	4589
65°	2534
70°	2651
75°	2069
80°	2139
85°	1880

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 39572 cd/sqm



TEST NUMBER: P748127

CATALOG NUMBER: LD4D40BD010-EU4DR6540509040-4LBDP1H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	330.6	9.5
10°-20°	953.6	27.3
20°-30°	1144.1	32.8
30°-40°	768.9	22.1
40°-50°	230.2	6.6
50°-60°	40.6	1.2
60°-70°	11.6	0.3
70°-80°	5.7	0.2
80°-90°	1.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2428.2	69.6
0°-40°	3197.1	91.7
0°-60°	3467.9	99.5
0°-90°	3486.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3486.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3433	
5°	3423	331
15°	3441	954
25°	2533	1144
35°	1238	769
45°	256	230
55°	42	41
65°	10	12
75°	5	6
85°	2	2
90°	0	



TEST NUMBER: P748127

CATALOG NUMBER: LD4D40BD010-EU4DR6540509040-4LBDP1H

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3433.0
2.5°	3447.7
5°	3422.8
7.5°	3474.5
10°	3502.8
12.5°	3496.0
15°	3441.3
17.5°	3307.7
20°	3082.3
22.5°	2816.9
25°	2533.0
27.5°	2212.4
30°	1852.9
32.5°	1527.0
35°	1238.2
37.5°	952.8
40°	683.5
42.5°	446.4
45°	256.1
47.5°	135.6
50°	84.4
52.5°	58.5
55°	42.0
57.5°	30.2
60°	21.0
62.5°	13.7
65°	9.8
67.5°	8.8
70°	8.3
72.5°	6.3
75°	4.9
77.5°	4.4
80°	3.4
82.5°	2.4
85°	1.5
87.5°	1.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)