

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P749726

Luminaire Tested: LD4D50D010-EU4DR7040509027-4LBDP1H

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P749726
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D50D010-EU4DR7040509027-4LBDP1H
Description: 4 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4741.7 lumens
Efficiency: N/A
Efficacy: 100.9 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 47
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P749726
CATALOG NUMBER: LD4D50D010-EU4DR7040509027-4LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P749726

CATALOG NUMBER: LD4D50D010-EU4DR7040509027-4LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	582480
5°	565171
10°	549417
15°	542206
20°	506310
25°	380366
30°	268880
35°	95249
40°	50077
45°	53340
50°	55243
55°	56271
60°	56619
65°	55429
70°	52295
75°	48463
80°	43038
85°	34976

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 56633 cd/sqm



TEST NUMBER: P749726

CATALOG NUMBER: LD4D50D010-EU4DR7040509027-4LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	486.0	10.3
10°-20°	1333.2	28.1
20°-30°	1468.3	31.0
30°-40°	561.0	11.8
40°-50°	264.9	5.6
50°-60°	263.3	5.6
60°-70°	210.8	4.4
70°-80°	121.2	2.6
80°-90°	33.0	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3287.5	69.3
0°-40°	3848.5	81.2
0°-60°	4376.7	92.3
0°-90°	4741.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4741.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5331	
5°	5153	486
15°	4793	1333
25°	3155	1468
35°	714	561
45°	345	265
55°	295	263
65°	214	211
75°	115	121
85°	28	33
90°	0	



TEST NUMBER: P749726

CATALOG NUMBER: LD4D50D010-EU4DR7040509027-4LBDP1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	5331.1
2.5°	5275.4
5°	5153.0
7.5°	5050.8
10°	4952.1
12.5°	4868.5
15°	4793.4
17.5°	4611.9
20°	4354.5
22.5°	3799.1
25°	3155.1
27.5°	2746.6
30°	2131.2
32.5°	1376.7
35°	714.1
37.5°	385.7
40°	351.1
42.5°	348.6
45°	345.2
47.5°	337.6
50°	325.0
52.5°	310.6
55°	295.4
57.5°	278.5
60°	259.1
62.5°	237.2
65°	214.4
67.5°	189.1
70°	163.7
72.5°	138.4
75°	114.8
77.5°	90.3
80°	68.4
82.5°	48.1
85°	27.9
87.5°	11.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)