

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P749727

Luminaire Tested: LD4D50D010-EU4DR7040509027-4LBDP1LI

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P749727
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D50D010-EU4DR7040509027-4LBDP1LI
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4978.7 lumens
Efficiency: N/A
Efficacy: 105.9 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 47
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P749727

CATALOG NUMBER: LD4D50D010-EU4DR7040509027-4LBDP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P749727

CATALOG NUMBER: LD4D50D010-EU4DR7040509027-4LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	611598
5°	593424
10°	576887
15°	569319
20°	531623
25°	399378
30°	282329
35°	100010
40°	52588
45°	56013
50°	57997
55°	59090
60°	59460
65°	58196
70°	54915
75°	50869
80°	45177
85°	36606

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 59480 cd/sqm



TEST NUMBER: P749727

CATALOG NUMBER: LD4D50D010-EU4DR7040509027-4LBDP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	510.3	10.3
10°-20°	1399.8	28.1
20°-30°	1541.7	31.0
30°-40°	589.1	11.8
40°-50°	278.1	5.6
50°-60°	276.5	5.6
60°-70°	221.4	4.4
70°-80°	127.2	2.6
80°-90°	34.6	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3451.9	69.3
0°-40°	4041.0	81.2
0°-60°	4595.6	92.3
0°-90°	4978.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4978.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5598	
5°	5411	510
15°	5033	1400
25°	3313	1542
35°	750	589
45°	362	278
55°	310	277
65°	225	221
75°	120	127
85°	29	35
90°	0	



TEST NUMBER: P749727

CATALOG NUMBER: LD4D50D010-EU4DR7040509027-4LBDP1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	5597.6
2.5°	5539.1
5°	5410.6
7.5°	5303.4
10°	5199.7
12.5°	5112.0
15°	5033.1
17.5°	4842.5
20°	4572.2
22.5°	3989.1
25°	3312.8
27.5°	2883.9
30°	2237.8
32.5°	1445.5
35°	749.8
37.5°	405.0
40°	368.7
42.5°	366.0
45°	362.5
47.5°	354.5
50°	341.2
52.5°	326.1
55°	310.2
57.5°	292.5
60°	272.1
62.5°	249.0
65°	225.1
67.5°	198.5
70°	171.9
72.5°	145.3
75°	120.5
77.5°	94.8
80°	71.8
82.5°	50.5
85°	29.2
87.5°	11.5
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)