

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P748860

Luminaire Tested: LD4D45BD010-EU4DR6540509024-4LBS1LI

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P748860
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D45BD010-EU4DR6540509024-4LBS1LI
Description: 4 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3419.8 lumens
Efficiency: N/A
Efficacy: 88.4 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct


Input Watts (W): 38.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P748860
CATALOG NUMBER: LD4D45BD010-EU4DR6540509024-4LBS1LI

Luminous Intensity Polar Plot





TEST NUMBER: P748860

CATALOG NUMBER: LD4D45BD010-EU4DR6540509024-4LBS1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100															
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93				93															
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85				85															
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78				78															
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72				72															
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66				66															
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61				61															
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56				56															
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52				52															
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49				49															
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46				46															

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	181350
5°	180888
10°	180737
15°	175165
20°	159464
25°	138962
30°	115577
35°	91582
40°	66101
45°	41760
50°	21770
55°	11567
60°	6074
65°	3344
70°	1400
75°	1534
80°	1076
85°	938

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 41760 cd/sqm



TEST NUMBER: P748860

CATALOG NUMBER: LD4D45BD010-EU4DR6540509024-4LBS1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	293.6	8.6
10°-20°	804.1	23.5
20°-30°	982.9	28.7
30°-40°	797.5	23.3
40°-50°	397.4	11.6
50°-60°	110.9	3.2
60°-70°	25.2	0.7
70°-80°	6.6	0.2
80°-90°	1.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2080.6	60.8
0°-40°	2878.1	84.2
0°-60°	3386.4	99.0
0°-90°	3419.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3419.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3105	
5°	3085	294
15°	2897	804
25°	2156	983
35°	1284	797
45°	506	397
55°	114	111
65°	24	25
75°	7	7
85°	1	2
90°	0	



TEST NUMBER: P748860

CATALOG NUMBER: LD4D45BD010-EU4DR6540509024-4LBS1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	3105.1
2.5°	3102.8
5°	3085.4
7.5°	3075.4
10°	3047.6
12.5°	2991.0
15°	2897.0
17.5°	2750.1
20°	2565.7
22.5°	2366.8
25°	2156.4
27.5°	1931.5
30°	1713.8
32.5°	1498.9
35°	1284.5
37.5°	1070.5
40°	867.0
42.5°	676.2
45°	505.6
47.5°	352.3
50°	239.6
52.5°	165.2
55°	113.6
57.5°	76.7
60°	52.0
62.5°	36.0
65°	24.2
67.5°	12.3
70°	8.2
72.5°	7.8
75°	6.8
77.5°	4.6
80°	3.2
82.5°	2.3
85°	1.4
87.5°	0.9
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)