

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P749676

Luminaire Tested: LD4D50D010-EU4DR6540509035-4LBDP1MW

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P749676  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D50D010-EU4DR6540509035-4LBDP1MW  
Description: 4 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 65° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3697.3 lumens  
Efficiency: N/A  
Efficacy: 78.7 lumens/watt  
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 47  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight

TEST NUMBER: P749676

CATALOG NUMBER: LD4D50D010-EU4DR6540509035-4LBDP1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P749676

CATALOG NUMBER: LD4D50D010-EU4DR6540509035-4LBDP1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93		
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87		
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80		
4	97	89	84	79	95	88	83	79	86	82	78	84	80	77	82	79	76	75		
5	92	83	78	73	90	83	77	73	81	76	72	79	75	72	77	74	71	69		
6	87	78	72	68	86	77	72	68	76	71	67	74	70	67	73	69	66	65		
7	83	73	67	63	81	73	67	63	71	66	62	70	66	62	69	65	62	60		
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	57		
9	75	65	59	55	74	65	59	55	64	58	55	63	58	55	62	58	54	53		
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50		

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	397731
5°	398066
10°	412077
15°	412757
20°	380015
25°	323789
30°	247873
35°	175118
40°	103364
45°	41967
50°	15213
55°	8477
60°	4851
65°	2663
70°	2811
75°	2195
80°	2265
85°	2006

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 41967 cd/sqm



TEST NUMBER: P749676

CATALOG NUMBER: LD4D50D010-EU4DR6540509035-4LBDP1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	350.5	9.5
10°-20°	1011.1	27.3
20°-30°	1213.1	32.8
30°-40°	815.2	22.0
40°-50°	244.0	6.6
50°-60°	43.1	1.2
60°-70°	12.2	0.3
70°-80°	6.0	0.2
80°-90°	1.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2574.8	69.6
0°-40°	3390.0	91.7
0°-60°	3677.1	99.5
0°-90°	3697.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3697.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3640	
5°	3629	351
15°	3649	1011
25°	2686	1213
35°	1313	815
45°	272	244
55°	44	43
65°	10	12
75°	5	6
85°	2	2
90°	0	



TEST NUMBER: P749676

CATALOG NUMBER: LD4D50D010-EU4DR6540509035-4LBDP1MW

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	3640.2
2.5°	3655.8
5°	3629.4
7.5°	3684.2
10°	3714.2
12.5°	3707.0
15°	3649.0
17.5°	3507.3
20°	3268.3
22.5°	2986.9
25°	2685.8
27.5°	2346.0
30°	1964.7
32.5°	1619.1
35°	1312.9
37.5°	1010.3
40°	724.7
42.5°	473.3
45°	271.6
47.5°	143.8
50°	89.5
52.5°	62.1
55°	44.5
57.5°	32.1
60°	22.2
62.5°	14.5
65°	10.3
67.5°	9.3
70°	8.8
72.5°	6.7
75°	5.2
77.5°	4.7
80°	3.6
82.5°	2.6
85°	1.6
87.5°	1.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)