

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P748884

Luminaire Tested: LD4D45BD010-EU4DR6540509030-4LBS1B

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P748884
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D45BD010-EU4DR6540509030-4LBS1B
Description: 4 INCH ROUND SHALLOW SPECULAR BLACK TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3529.0 lumens
Efficiency: N/A
Efficacy: 91.2 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct

Input Watts (W): 38.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P748884

CATALOG NUMBER: LD4D45BD010-EU4DR6540509030-4LBS1B

Luminous Intensity Polar Plot





TEST NUMBER: P748884

CATALOG NUMBER: LD4D45BD010-EU4DR6540509030-4LBS1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93																			
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85																			
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78																			
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72																			
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66																			
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61																			
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56																			
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52																			
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49																			
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	187138
5°	186668
10°	186508
15°	180758
20°	164554
25°	143402
30°	119273
35°	94505
40°	68205
45°	43090
50°	22461
55°	11934
60°	6273
65°	3455
70°	1451
75°	1602
80°	1110
85°	938

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 43090 cd/sqm



TEST NUMBER: P748884

CATALOG NUMBER: LD4D45BD010-EU4DR6540509030-4LBS1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	303.0	8.6
10°-20°	829.8	23.5
20°-30°	1014.3	28.7
30°-40°	822.9	23.3
40°-50°	410.1	11.6
50°-60°	114.4	3.2
60°-70°	26.0	0.7
70°-80°	6.8	0.2
80°-90°	1.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2147.1	60.8
0°-40°	2970.0	84.2
0°-60°	3494.5	99.0
0°-90°	3529.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3529.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3204	
5°	3184	303
15°	2990	830
25°	2225	1014
35°	1326	823
45°	522	410
55°	117	114
65°	25	26
75°	7	7
85°	1	2
90°	0	



TEST NUMBER: P748884

CATALOG NUMBER: LD4D45BD010-EU4DR6540509030-4LBS1B

CANDELA DISTRIBUTION (FULL):

0°	
0°	3204.2
2.5°	3201.9
5°	3184.0
7.5°	3173.6
10°	3144.9
12.5°	3086.5
15°	2989.5
17.5°	2837.9
20°	2647.6
22.5°	2442.4
25°	2225.3
27.5°	1993.2
30°	1768.6
32.5°	1546.8
35°	1325.5
37.5°	1104.6
40°	894.6
42.5°	697.8
45°	521.7
47.5°	363.5
50°	247.2
52.5°	170.5
55°	117.2
57.5°	79.1
60°	53.7
62.5°	37.2
65°	25.0
67.5°	12.7
70°	8.5
72.5°	8.0
75°	7.1
77.5°	4.7
80°	3.3
82.5°	2.4
85°	1.4
87.5°	0.9
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)