

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P748885

Luminaire Tested: LD4D45BD010-EU4DR6540509030-4LBS1H

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P748885
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D45BD010-EU4DR6540509030-4LBS1H
Description: 4 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3800.8 lumens
Efficiency: N/A
Efficacy: 98.2 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct

Input Watts (W): 38.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P748885

CATALOG NUMBER: LD4D45BD010-EU4DR6540509030-4LBS1H

Luminous Intensity Polar Plot





TEST NUMBER: P748885
 CATALOG NUMBER: LD4D45BD010-EU4DR6540509030-4LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93																			
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85																			
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78																			
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72																			
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66																			
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61																			
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56																			
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52																			
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49																			
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	201558
5°	201049
10°	200877
15°	194682
20°	177233
25°	154447
30°	128458
35°	101785
40°	73466
45°	46410
50°	24187
55°	12860
60°	6751
65°	3717
70°	1554
75°	1715
80°	1177
85°	1005

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 46410 cd/sqm



TEST NUMBER: P748885

CATALOG NUMBER: LD4D45BD010-EU4DR6540509030-4LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	326.4	8.6
10°-20°	893.7	23.5
20°-30°	1092.4	28.7
30°-40°	886.4	23.3
40°-50°	441.7	11.6
50°-60°	123.2	3.2
60°-70°	28.0	0.7
70°-80°	7.3	0.2
80°-90°	1.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2312.5	60.8
0°-40°	3198.8	84.2
0°-60°	3763.7	99.0
0°-90°	3800.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3800.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3451	
5°	3429	326
15°	3220	894
25°	2397	1092
35°	1428	886
45°	562	442
55°	126	123
65°	27	28
75°	8	7
85°	2	2
90°	0	



TEST NUMBER: P748885

CATALOG NUMBER: LD4D45BD010-EU4DR6540509030-4LBS1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	3451.1
2.5°	3448.6
5°	3429.3
7.5°	3418.1
10°	3387.2
12.5°	3324.3
15°	3219.8
17.5°	3056.5
20°	2851.6
22.5°	2630.5
25°	2396.7
27.5°	2146.7
30°	1904.8
32.5°	1666.0
35°	1427.6
37.5°	1189.8
40°	963.6
42.5°	751.6
45°	561.9
47.5°	391.5
50°	266.2
52.5°	183.6
55°	126.3
57.5°	85.2
60°	57.8
62.5°	40.1
65°	26.9
67.5°	13.7
70°	9.1
72.5°	8.6
75°	7.6
77.5°	5.1
80°	3.5
82.5°	2.5
85°	1.5
87.5°	1.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)