

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P749765

Luminaire Tested: LD4D50D010-EU4DR7040509040-4LBDP1H

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P749765
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D50D010-EU4DR7040509040-4LBDP1H
Description: 4 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5167.2 lumens
Efficiency: N/A
Efficacy: 109.9 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 47
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P749765
CATALOG NUMBER: LD4D50D010-EU4DR7040509040-4LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P749765

CATALOG NUMBER: LD4D50D010-EU4DR7040509040-4LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91					91			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83					83			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76					76			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70					70			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65					65			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61					61			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57					57			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53					53			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50					50			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48					48			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	634750
5°	615886
10°	598722
15°	590868
20°	551750
25°	414495
30°	293015
35°	103798
40°	54570
45°	58130
50°	60190
55°	61319
60°	61710
65°	60393
70°	56991
75°	52811
80°	46876
85°	38110

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 61717 cd/sqm



TEST NUMBER: P749765

CATALOG NUMBER: LD4D50D010-EU4DR7040509040-4LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	529.7	10.3
10°-20°	1452.8	28.1
20°-30°	1600.1	31.0
30°-40°	611.4	11.8
40°-50°	288.7	5.6
50°-60°	287.0	5.6
60°-70°	229.8	4.4
70°-80°	132.0	2.6
80°-90°	35.9	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3582.6	69.3
0°-40°	4193.9	81.2
0°-60°	4769.5	92.3
0°-90°	5167.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5167.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5810	
5°	5615	530
15°	5224	1453
25°	3438	1600
35°	778	611
45°	376	289
55°	322	287
65°	234	230
75°	125	132
85°	30	36
90°	0	



TEST NUMBER: P749765

CATALOG NUMBER: LD4D50D010-EU4DR7040509040-4LBDP1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	5809.5
2.5°	5748.8
5°	5615.4
7.5°	5504.1
10°	5396.5
12.5°	5305.5
15°	5223.6
17.5°	5025.8
20°	4745.3
22.5°	4140.1
25°	3438.2
27.5°	2993.1
30°	2322.5
32.5°	1500.2
35°	778.2
37.5°	420.4
40°	382.6
42.5°	379.9
45°	376.2
47.5°	367.9
50°	354.1
52.5°	338.5
55°	321.9
57.5°	303.5
60°	282.4
62.5°	258.5
65°	233.6
67.5°	206.0
70°	178.4
72.5°	150.8
75°	125.1
77.5°	98.4
80°	74.5
82.5°	52.4
85°	30.4
87.5°	12.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)