

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P748987

Luminaire Tested: LD4D45BD010-EU4DR7040509040-4LBDP1MW

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P748987  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D45BD010-EU4DR7040509040-4LBDP1MW  
Description: 4 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 70° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3436.8 lumens  
Efficiency: N/A  
Efficacy: 88.8 lumens/watt  
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct


Input Watts (W): 38.7  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



Downlight

TEST NUMBER: P748987  
CATALOG NUMBER: LD4D45BD010-EU4DR7040509040-4LBDP1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P748987

CATALOG NUMBER: LD4D45BD010-EU4DR7040509040-4LBDP1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10		0		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	422173
5°	409626
10°	398208
15°	392984
20°	366969
25°	275687
30°	194885
35°	69026
40°	36299
45°	38660
50°	40030
55°	40784
60°	41038
65°	40176
70°	37920
75°	35123
80°	31209
85°	25323

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 57.5°  
 Luminance: 41057 cd/sqm



TEST NUMBER: P748987

CATALOG NUMBER: LD4D45BD010-EU4DR7040509040-4LBDP1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	352.3	10.3
10°-20°	966.3	28.1
20°-30°	1064.2	31.0
30°-40°	406.6	11.8
40°-50°	192.0	5.6
50°-60°	190.9	5.6
60°-70°	152.8	4.4
70°-80°	87.8	2.6
80°-90°	23.9	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2382.8	69.3
0°-40°	2789.4	81.2
0°-60°	3172.2	92.3
0°-90°	3436.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3436.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3864	
5°	3735	352
15°	3474	966
25°	2287	1064
35°	518	407
45°	250	192
55°	214	191
65°	155	153
75°	83	88
85°	20	24
90°	0	



TEST NUMBER: P748987

CATALOG NUMBER: LD4D45BD010-EU4DR7040509040-4LBDP1MW

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	3863.9
2.5°	3823.5
5°	3734.8
7.5°	3660.8
10°	3589.2
12.5°	3528.6
15°	3474.2
17.5°	3342.7
20°	3156.1
22.5°	2753.5
25°	2286.8
27.5°	1990.7
30°	1544.7
32.5°	997.8
35°	517.5
37.5°	279.6
40°	254.5
42.5°	252.7
45°	250.2
47.5°	244.7
50°	235.5
52.5°	225.1
55°	214.1
57.5°	201.9
60°	187.8
62.5°	171.9
65°	155.4
67.5°	137.0
70°	118.7
72.5°	100.3
75°	83.2
77.5°	65.5
80°	49.6
82.5°	34.9
85°	20.2
87.5°	8.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)