

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P750337

Luminaire Tested: LD4D55D010-EU4DR6055659024-4LBDP1H

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P750337
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D55D010-EU4DR6055659024-4LBDP1H
Description: 4 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4701.8 lumens
Efficiency: N/A
Efficacy: 80.8 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 58.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P750337
CATALOG NUMBER: LD4D55D010-EU4DR6055659024-4LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P750337

CATALOG NUMBER: LD4D55D010-EU4DR6055659024-4LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93																			
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86																			
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80																			
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70																			
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66																			
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62																			
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59																			
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55																			
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	610112
5°	625110
10°	632660
15°	602700
20°	531390
25°	429806
30°	290731
35°	145681
40°	23634
45°	23131
50°	23593
55°	23945
60°	24606
65°	25181
70°	25780
75°	26089
80°	25168
85°	20936

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 26089 cd/sqm



TEST NUMBER: P750337

CATALOG NUMBER: LD4D55D010-EU4DR6055659024-4LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	544.7	11.6
10°-20°	1473.8	31.3
20°-30°	1585.7	33.7
30°-40°	689.3	14.7
40°-50°	115.8	2.5
50°-60°	112.6	2.4
60°-70°	96.3	2.0
70°-80°	64.4	1.4
80°-90°	19.3	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3604.2	76.7
0°-40°	4293.5	91.3
0°-60°	4521.8	96.2
0°-90°	4701.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4701.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5584	
5°	5700	545
15°	5328	1474
25°	3565	1586
35°	1092	689
45°	150	116
55°	126	113
65°	97	96
75°	62	64
85°	17	19
90°	0	



TEST NUMBER: P750337

CATALOG NUMBER: LD4D55D010-EU4DR6055659024-4LBDP1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	5584.0
2.5°	5740.9
5°	5699.5
7.5°	5712.6
10°	5702.4
12.5°	5584.7
15°	5328.2
17.5°	4983.7
20°	4570.2
22.5°	4127.6
25°	3565.2
27.5°	2851.6
30°	2304.4
32.5°	1776.1
35°	1092.2
37.5°	467.3
40°	165.7
42.5°	152.6
45°	149.7
47.5°	144.6
50°	138.8
52.5°	132.3
55°	125.7
57.5°	119.2
60°	112.6
62.5°	105.4
65°	97.4
67.5°	89.4
70°	80.7
72.5°	71.2
75°	61.8
77.5°	50.9
80°	40.0
82.5°	28.3
85°	16.7
87.5°	5.8
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)