

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P749972

Luminaire Tested: LD4D55D010-EU4DR3555659030-4LBDP1B

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P749972
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-20)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D55D010-EU4DR3555659030-4LBDP1B
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 35° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4523.7 lumens
Efficiency: N/A
Efficacy: 77.7 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.54
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 58.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P749972

CATALOG NUMBER: LD4D55D010-EU4DR3555659030-4LBDP1B

Luminous Intensity Polar Plot





TEST NUMBER: P749972

CATALOG NUMBER: LD4D55D010-EU4DR3555659030-4LBDP1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20								
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR	0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	99	98	98	96	96	95	93	92																
	1	115	112	110	108	112	110	108	107	106	105	103	103	101	100	99	98	98	96	96	95	93	92	92	91	89	88	88	84																
	2	110	106	103	101	108	105	102	99	102	99	97	99	97	95	96	95	93	92	92	91	89	88	88	86	84	81	81	78																
	3	106	101	97	94	105	100	96	93	97	95	92	95	93	91	93	91	89	88	88	86	84	81	81	78	75	75	72	72																
	4	103	97	92	89	101	96	92	89	94	90	88	92	89	87	90	88	86	84	81	81	78	75	75	72	72	70	70	68																
	5	99	93	88	85	98	92	87	84	90	86	84	89	85	83	87	84	82	81	78	78	75	75	72	72	70	68	68	68																
	6	96	89	84	81	94	88	84	81	87	83	80	85	82	80	84	81	79	78	78	75	75	72	72	70	68	68	68	68																
	7	93	85	81	78	91	85	80	77	84	80	77	83	79	77	82	79	76	75	75	72	72	70	68	68	68	68	68	68																
	8	90	82	78	74	88	82	77	74	81	77	74	80	76	74	79	76	73	72	72	70	68	68	68	68	68	68	68	68																
	9	87	79	75	72	86	79	75	72	78	74	71	77	74	71	77	73	71	70	70	68	68	68	68	68	68	68	68	68																
	10	84	77	72	69	83	76	72	69	76	72	69	75	71	69	74	71	69	68	68	68	68	68	68	68	68	68	68	68																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1359947
5°	1327994
10°	1196877
15°	928969
20°	526890
25°	204981
30°	76480
35°	41922
40°	27399
45°	16672
50°	10607
55°	7505
60°	5485
65°	2973
70°	224
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 16672 cd/sqm



TEST NUMBER: P749972

CATALOG NUMBER: LD4D55D010-EU4DR3555659030-4LBDP1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1113.6	24.6
10°-20°	2174.2	48.1
20°-30°	886.7	19.6
30°-40°	212.2	4.7
40°-50°	88.4	2.0
50°-60°	36.6	0.8
60°-70°	11.4	0.3
70°-80°	0.3	0.0
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4174.5	92.3
0°-40°	4386.7	97.0
0°-60°	4511.8	99.7
0°-90°	4523.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4523.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	12447	
5°	12108	###
15°	8213	2174
25°	1700	887
35°	314	212
45°	108	88
55°	39	37
65°	12	11
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P749972

CATALOG NUMBER: LD4D55D010-EU4DR3555659030-4LBDP1B

CANDELA DISTRIBUTION (FULL):

0°	
0°	12446.8
2.5°	12372.1
5°	12108.1
7.5°	11581.4
10°	10787.9
12.5°	9670.6
15°	8212.6
17.5°	6429.4
20°	4531.5
22.5°	2889.6
25°	1700.3
27.5°	961.2
30°	606.2
32.5°	425.6
35°	314.3
37.5°	243.0
40°	192.1
42.5°	148.0
45°	107.9
47.5°	80.8
50°	62.4
52.5°	49.6
55°	39.4
57.5°	31.9
60°	25.1
62.5°	18.3
65°	11.5
67.5°	4.1
70°	0.7
72.5°	0.7
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.7
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)