

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P740555

Luminaire Tested: LD4D05D010-EU4DR600210IC9027-4LBDP1LI

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P740555
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D05D010-EU4DR600210IC9027-4LBDP1LI
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 647.9 lumens
Efficiency: N/A
Efficacy: 86.4 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.84
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 7.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P740555

CATALOG NUMBER: LD4D05D010-EU4DR600210IC9027-4LBDP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P740555

CATALOG NUMBER: LD4D05D010-EU4DR600210IC9027-4LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93			93																
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86			86																
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80			80																
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75			75																
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70			70																
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66			66																
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62			62																
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59			59																
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55			55																
10	73	64	58	54	72	63	58	54	63	58	54	62	57	54	61	57	54	53			53																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	84076
5°	86152
10°	87193
15°	83060
20°	73229
25°	59229
30°	40070
35°	20074
40°	3266
45°	3183
50°	3247
55°	3295
60°	3387
65°	3464
70°	3546
75°	3588
80°	3461
85°	2883

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 3588 cd/sqm



TEST NUMBER: P740555

CATALOG NUMBER: LD4D05D010-EU4DR600210IC9027-4LBDP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	75.1	11.6
10°-20°	203.1	31.3
20°-30°	218.5	33.7
30°-40°	95.0	14.7
40°-50°	15.9	2.5
50°-60°	15.5	2.4
60°-70°	13.2	2.0
70°-80°	8.9	1.4
80°-90°	2.7	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	496.7	76.7
0°-40°	591.7	91.3
0°-60°	623.1	96.2
0°-90°	647.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	647.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	770	
5°	786	75
15°	734	203
25°	491	219
35°	150	95
45°	21	16
55°	17	15
65°	13	13
75°	8	9
85°	2	3
90°	0	



TEST NUMBER: P740555

CATALOG NUMBER: LD4D05D010-EU4DR600210IC9027-4LBDP1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	769.5
2.5°	791.2
5°	785.5
7.5°	787.3
10°	785.9
12.5°	769.6
15°	734.3
17.5°	686.8
20°	629.8
22.5°	568.8
25°	491.3
27.5°	393.0
30°	317.6
32.5°	244.8
35°	150.5
37.5°	64.4
40°	22.9
42.5°	21.0
45°	20.6
47.5°	19.9
50°	19.1
52.5°	18.2
55°	17.3
57.5°	16.4
60°	15.5
62.5°	14.5
65°	13.4
67.5°	12.3
70°	11.1
72.5°	9.8
75°	8.5
77.5°	7.0
80°	5.5
82.5°	3.9
85°	2.3
87.5°	0.8
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)