

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P740648

Luminaire Tested: LD4D05D010-EU4DR650210IC9030-4LBS1B

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P740648
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D05D010-EU4DR650210IC9030-4LBS1B
Description: 4 INCH ROUND SHALLOW SPECULAR BLACK TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 544.1 lumens
Efficiency: N/A
Efficacy: 72.5 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct

Input Watts (W): 7.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P740648
CATALOG NUMBER: LD4D05D010-EU4DR650210IC9030-4LBS1B

Luminous Intensity Polar Plot





TEST NUMBER: P740648

CATALOG NUMBER: LD4D05D010-EU4DR650210IC9030-4LBS1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						100													
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93						93													
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85						85													
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78						78													
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72						72													
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66						66													
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61						61													
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56						56													
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52						52													
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49						49													
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46						46													

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	28857
5°	28786
10°	28757
15°	27868
20°	25370
25°	22110
30°	18391
35°	14573
40°	10521
45°	6641
50°	3462
55°	1843
60°	970
65°	525
70°	222
75°	248
80°	168
85°	134

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 6641 cd/sqm



TEST NUMBER: P740648

CATALOG NUMBER: LD4D05D010-EU4DR650210IC9030-4LBS1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	46.7	8.6
10°-20°	127.9	23.5
20°-30°	156.4	28.7
30°-40°	126.9	23.3
40°-50°	63.2	11.6
50°-60°	17.6	3.2
60°-70°	4.0	0.7
70°-80°	1.1	0.2
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	331.0	60.8
0°-40°	457.9	84.2
0°-60°	538.8	99.0
0°-90°	544.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	544.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	494	
5°	491	47
15°	461	128
25°	343	156
35°	204	127
45°	80	63
55°	18	18
65°	4	4
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P740648
CATALOG NUMBER: LD4D05D010-EU4DR650210IC9030-4LBS1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	494.1
2.5°	493.7
5°	491.0
7.5°	489.4
10°	484.9
12.5°	475.9
15°	460.9
17.5°	437.6
20°	408.2
22.5°	376.6
25°	343.1
27.5°	307.3
30°	272.7
32.5°	238.5
35°	204.4
37.5°	170.3
40°	138.0
42.5°	107.6
45°	80.4
47.5°	56.0
50°	38.1
52.5°	26.3
55°	18.1
57.5°	12.2
60°	8.3
62.5°	5.7
65°	3.8
67.5°	1.9
70°	1.3
72.5°	1.3
75°	1.1
77.5°	0.7
80°	0.5
82.5°	0.3
85°	0.2
87.5°	0.2
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)