

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P740725

Luminaire Tested: LD4D05D010-EU4DR700210IC9030-4LBDP1MW

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P740725
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D05D010-EU4DR700210IC9030-4LBDP1MW
Description: 4 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 500.9 lumens
Efficiency: N/A
Efficacy: 66.8 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 7.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P740725

CATALOG NUMBER: LD4D05D010-EU4DR700210IC9030-4LBDP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P740725

CATALOG NUMBER: LD4D05D010-EU4DR700210IC9030-4LBDP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	88	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	61547
5°	59709
10°	58047
15°	57281
20°	53497
25°	40181
30°	28412
35°	10070
40°	5292
45°	5640
50°	5830
55°	5943
60°	5987
65°	5843
70°	5527
75°	5108
80°	4530
85°	3636

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 60°
 Luminance: 5987 cd/sqm



TEST NUMBER: P740725

CATALOG NUMBER: LD4D05D010-EU4DR700210IC9030-4LBDP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	51.3	10.3
10°-20°	140.9	28.1
20°-30°	155.1	31.0
30°-40°	59.3	11.8
40°-50°	28.0	5.6
50°-60°	27.8	5.6
60°-70°	22.3	4.4
70°-80°	12.8	2.6
80°-90°	3.5	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	347.3	69.3
0°-40°	406.6	81.2
0°-60°	462.4	92.3
0°-90°	500.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	500.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	563	
5°	544	51
15°	506	141
25°	333	155
35°	76	59
45°	36	28
55°	31	28
65°	23	22
75°	12	13
85°	3	3
90°	0	



TEST NUMBER: P740725

CATALOG NUMBER: LD4D05D010-EU4DR700210IC9030-4LBDP1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	563.3
2.5°	557.4
5°	544.4
7.5°	533.6
10°	523.2
12.5°	514.4
15°	506.4
17.5°	487.3
20°	460.1
22.5°	401.4
25°	333.3
27.5°	290.2
30°	225.2
32.5°	145.5
35°	75.5
37.5°	40.7
40°	37.1
42.5°	36.8
45°	36.5
47.5°	35.7
50°	34.3
52.5°	32.8
55°	31.2
57.5°	29.4
60°	27.4
62.5°	25.0
65°	22.6
67.5°	20.0
70°	17.3
72.5°	14.6
75°	12.1
77.5°	9.6
80°	7.2
82.5°	5.1
85°	2.9
87.5°	1.1
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)