

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P750533

Luminaire Tested: LD4D55D010-EU4DR7055659035-4LBDP1LI

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P750533  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D55D010-EU4DR7055659035-4LBDP1LI  
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 70° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5860.3 lumens  
Efficiency: N/A  
Efficacy: 100.7 lumens/watt  
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct


Input Watts (W): 58.2  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



Downlight

TEST NUMBER: P750533  
CATALOG NUMBER: LD4D55D010-EU4DR7055659035-4LBDP1LI

### Luminous Intensity Polar Plot





TEST NUMBER: P750533

CATALOG NUMBER: LD4D55D010-EU4DR7055659035-4LBDP1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	719875
5°	698485
10°	679013
15°	670105
20°	625746
25°	470084
30°	332315
35°	117710
40°	61901
45°	65933
50°	68264
55°	69548
60°	69992
65°	68511
70°	64658
75°	59903
80°	53168
85°	43125

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 57.5°  
 Luminance: 69994 cd/sqm



TEST NUMBER: P750533

CATALOG NUMBER: LD4D55D010-EU4DR7055659035-4LBDP1LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	600.7	10.3
10°-20°	1647.7	28.1
20°-30°	1814.7	31.0
30°-40°	693.3	11.8
40°-50°	327.4	5.6
50°-60°	325.5	5.6
60°-70°	260.6	4.4
70°-80°	149.8	2.6
80°-90°	40.7	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4063.0	69.3
0°-40°	4756.3	81.2
0°-60°	5409.2	92.3
0°-90°	5860.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5860.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	6589	
5°	6368	601
15°	5924	1648
25°	3899	1815
35°	882	693
45°	427	327
55°	365	325
65°	265	261
75°	142	150
85°	34	41
90°	0	



TEST NUMBER: P750533

CATALOG NUMBER: LD4D55D010-EU4DR7055659035-4LBDP1LI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	6588.6
2.5°	6519.8
5°	6368.5
7.5°	6242.3
10°	6120.2
12.5°	6017.0
15°	5924.1
17.5°	5699.8
20°	5381.7
22.5°	4695.3
25°	3899.3
27.5°	3394.4
30°	2634.0
32.5°	1701.4
35°	882.5
37.5°	476.7
40°	434.0
42.5°	430.8
45°	426.7
47.5°	417.3
50°	401.6
52.5°	383.9
55°	365.1
57.5°	344.2
60°	320.3
62.5°	293.1
65°	265.0
67.5°	233.7
70°	202.4
72.5°	171.1
75°	141.9
77.5°	111.6
80°	84.5
82.5°	59.5
85°	34.4
87.5°	13.6
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)