

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P740729

Luminaire Tested: LD4D05D010-EU4DR700210IC9030-4LBS1MW

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P740729
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-76)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D05D010-EU4DR700210IC9030-4LBS1MW
Description: 4 INCH ROUND SHALLOW MATTE WHITE TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 641.2 lumens
Efficiency: N/A
Efficacy: 85.5 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.04
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 7.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P740729
CATALOG NUMBER: LD4D05D010-EU4DR700210IC9030-4LBS1MW

Luminous Intensity Polar Plot





TEST NUMBER: P740729

CATALOG NUMBER: LD4D05D010-EU4DR700210IC9030-4LBS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR	0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	99	97	97	95	94	93											
	1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	95	94	93	93	92	90	94	91	88	91	89	87	85								
	2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85	85	82	79	85	82	79	78	78	78									
	3	101	94	88	84	99	92	87	83	90	85	82	87	84	81	85	82	79	78	78	76	74	79	76	73	71	71	71									
	4	95	87	81	76	93	86	80	76	83	78	75	81	77	74	79	76	73	71	71	68	67	65	62	60	60	60	60									
	5	89	80	74	69	88	79	73	69	78	72	68	76	71	68	74	70	67	65	65	62	60	57	55	53	51	51	51									
	6	84	75	68	63	83	74	68	63	72	67	63	71	66	62	69	65	62	60	60	57	55	53	51	49	48	48	48									
	7	80	69	63	58	78	69	62	58	67	62	58	66	61	57	65	61	57	56	56	53	51	49	48	46	44	44	44									
	8	75	65	58	54	74	64	58	54	63	57	53	62	57	53	61	56	53	51	51	49	48	46	44	42	42	42	42									
	9	71	61	54	50	70	60	54	50	59	53	50	58	53	49	57	53	49	48	48	46	44	42	40	38	38	38	38									
	10	67	57	50	46	66	56	50	46	55	50	46	55	50	46	54	49	46	44	44	42	40	38	36	34	34	34	34									

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	55286
5°	55146
10°	55029
15°	55019
20°	54474
25°	51176
30°	45621
35°	36373
40°	24161
45°	14432
50°	7496
55°	3943
60°	1399
65°	26
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 14432 cd/sqm



TEST NUMBER: P740729

CATALOG NUMBER: LD4D05D010-EU4DR700210IC9030-4LBS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	47.8	7.5
10°-20°	137.1	21.4
20°-30°	193.5	30.2
30°-40°	167.0	26.1
40°-50°	74.8	11.7
50°-60°	19.6	3.1
60°-70°	1.3	0.2
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	378.4	59.0
0°-40°	545.5	85.1
0°-60°	639.9	99.8
0°-90°	641.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	641.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	506	
5°	503	48
15°	486	137
25°	424	193
35°	273	167
45°	93	75
55°	21	20
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P740729

CATALOG NUMBER: LD4D05D010-EU4DR700210IC9030-4LBS1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	506.0
2.5°	505.5
5°	502.8
7.5°	500.6
10°	496.0
12.5°	491.8
15°	486.4
17.5°	480.1
20°	468.5
22.5°	449.5
25°	424.5
27.5°	395.5
30°	361.6
32.5°	320.2
35°	272.7
37.5°	220.3
40°	169.4
42.5°	128.7
45°	93.4
47.5°	64.4
50°	44.1
52.5°	30.4
55°	20.7
57.5°	12.5
60°	6.4
62.5°	2.0
65°	0.1
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)