

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P750473

Luminaire Tested: LD4D55D010-EU4DR6555659040-4LBS1MW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P750473
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D55D010-EU4DR6555659040-4LBS1MW
Description: 4 INCH ROUND SHALLOW MATTE WHITE TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5072.7 lumens
Efficiency: N/A
Efficacy: 87.2 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct


Input Watts (W): 58.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P750473
CATALOG NUMBER: LD4D55D010-EU4DR6555659040-4LBS1MW

Luminous Intensity Polar Plot





TEST NUMBER: P750473
 CATALOG NUMBER: LD4D55D010-EU4DR6555659040-4LBS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93																			
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85																			
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78																			
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72																			
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66																			
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61																			
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56																			
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52																			
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49																			
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	268997
5°	268318
10°	268088
15°	259826
20°	236538
25°	206129
30°	171443
35°	135844
40°	98046
45°	61938
50°	32283
55°	17157
60°	9018
65°	4961
70°	2083
75°	2302
80°	1581
85°	1340

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 61938 cd/sqm



TEST NUMBER: P750473

CATALOG NUMBER: LD4D55D010-EU4DR6555659040-4LBS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	435.6	8.6
10°-20°	1192.7	23.5
20°-30°	1457.9	28.7
30°-40°	1182.9	23.3
40°-50°	589.5	11.6
50°-60°	164.4	3.2
60°-70°	37.4	0.7
70°-80°	9.7	0.2
80°-90°	2.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3086.2	60.8
0°-40°	4269.2	84.2
0°-60°	5023.1	99.0
0°-90°	5072.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5072.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4606	
5°	4577	436
15°	4297	1193
25°	3199	1458
35°	1905	1183
45°	750	589
55°	168	164
65°	36	37
75°	10	10
85°	2	2
90°	0	



TEST NUMBER: P750473

CATALOG NUMBER: LD4D55D010-EU4DR6555659040-4LBS1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	4605.8
2.5°	4602.4
5°	4576.7
7.5°	4561.8
10°	4520.5
12.5°	4436.6
15°	4297.2
17.5°	4079.2
20°	3805.8
22.5°	3510.7
25°	3198.7
27.5°	2865.0
30°	2542.2
32.5°	2223.4
35°	1905.3
37.5°	1587.8
40°	1286.0
42.5°	1003.1
45°	749.9
47.5°	522.5
50°	355.3
52.5°	245.0
55°	168.5
57.5°	113.7
60°	77.2
62.5°	53.5
65°	35.9
67.5°	18.3
70°	12.2
72.5°	11.5
75°	10.2
77.5°	6.8
80°	4.7
82.5°	3.4
85°	2.0
87.5°	1.4
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)