

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P751974

Luminaire Tested: LD4D65D010-EU4DR6555659024-4LBDP1B

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P751974  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D65D010-EU4DR6555659024-4LBDP1B  
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 65° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3721.8 lumens  
Efficiency: N/A  
Efficacy: 51.1 lumens/watt  
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct


Input Watts (W): 72.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



Downlight

TEST NUMBER: P751974  
CATALOG NUMBER: LD4D65D010-EU4DR6555659024-4LBDP1B

### Luminous Intensity Polar Plot





TEST NUMBER: P751974

CATALOG NUMBER: LD4D65D010-EU4DR6555659024-4LBDP1B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93			
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87			
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80			
4	97	89	84	79	95	88	83	79	86	82	78	84	80	77	82	79	76	75			
5	92	83	78	73	90	83	77	73	81	76	72	79	75	72	77	74	71	69			
6	87	78	72	68	86	77	72	68	76	71	67	74	70	67	73	69	66	65			
7	83	73	67	63	81	73	67	63	71	66	62	70	66	62	69	65	62	60			
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	57			
9	75	65	59	55	74	65	59	55	64	58	55	63	58	55	62	58	54	53			
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	400375
5°	400698
10°	414806
15°	415494
20°	382538
25°	325935
30°	249513
35°	176279
40°	104048
45°	42245
50°	15315
55°	8534
60°	4895
65°	2689
70°	2843
75°	2195
80°	2265
85°	2006

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 42245 cd/sqm



TEST NUMBER: P751974

CATALOG NUMBER: LD4D65D010-EU4DR6555659024-4LBDP1B

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	352.8	9.5
10°-20°	1017.8	27.3
20°-30°	1221.2	32.8
30°-40°	820.7	22.0
40°-50°	245.7	6.6
50°-60°	43.4	1.2
60°-70°	12.3	0.3
70°-80°	6.1	0.2
80°-90°	1.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2591.8	69.6
0°-40°	3412.5	91.7
0°-60°	3701.5	99.5
0°-90°	3721.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3721.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3664	
5°	3653	353
15°	3673	1018
25°	2704	1221
35°	1322	821
45°	273	246
55°	45	43
65°	10	12
75°	5	6
85°	2	2
90°	0	



TEST NUMBER: P751974

CATALOG NUMBER: LD4D65D010-EU4DR6555659024-4LBDP1B

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3664.4
2.5°	3680.0
5°	3653.4
7.5°	3708.6
10°	3738.8
12.5°	3731.5
15°	3673.2
17.5°	3530.5
20°	3290.0
22.5°	3006.7
25°	2703.6
27.5°	2361.5
30°	1977.7
32.5°	1629.9
35°	1321.6
37.5°	1017.0
40°	729.5
42.5°	476.5
45°	273.4
47.5°	144.8
50°	90.1
52.5°	62.5
55°	44.8
57.5°	32.3
60°	22.4
62.5°	14.6
65°	10.4
67.5°	9.4
70°	8.9
72.5°	6.8
75°	5.2
77.5°	4.7
80°	3.6
82.5°	2.6
85°	1.6
87.5°	1.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)