

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P751975

Luminaire Tested: LD4D65D010-EU4DR6555659024-4LBDP1H

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P751975
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D65D010-EU4DR6555659024-4LBDP1H
Description: 4 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4996.4 lumens
Efficiency: N/A
Efficacy: 68.6 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 72.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P751975
CATALOG NUMBER: LD4D65D010-EU4DR6555659024-4LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P751975
 CATALOG NUMBER: LD4D65D010-EU4DR6555659024-4LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93																			
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87																			
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80																			
4	97	89	84	79	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	83	78	73	90	83	77	73	81	76	72	79	75	72	77	74	71	69																			
6	87	78	72	68	86	77	72	68	76	71	67	74	70	67	73	69	66	65																			
7	83	73	67	63	81	73	67	63	71	66	62	70	66	62	69	65	62	60																			
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	57																			
9	75	65	59	55	74	65	59	55	64	58	55	63	58	55	62	58	54	53																			
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	537486
5°	537927
10°	556873
15°	557793
20°	513542
25°	437558
30°	334964
35°	236648
40°	139692
45°	56708
50°	20551
55°	11448
60°	6577
65°	3619
70°	3802
75°	2955
80°	3083
85°	2633

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 56708 cd/sqm



TEST NUMBER: P751975
 CATALOG NUMBER: LD4D65D010-EU4DR6555659024-4LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	473.7	9.5
10°-20°	1366.4	27.3
20°-30°	1639.4	32.8
30°-40°	1101.7	22.1
40°-50°	329.8	6.6
50°-60°	58.2	1.2
60°-70°	16.6	0.3
70°-80°	8.1	0.2
80°-90°	2.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3479.5	69.6
0°-40°	4581.2	91.7
0°-60°	4969.2	99.5
0°-90°	4996.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4996.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4919	
5°	4905	474
15°	4931	1366
25°	3630	1639
35°	1774	1102
45°	367	330
55°	60	58
65°	14	17
75°	7	8
85°	2	3
90°	0	



TEST NUMBER: P751975

CATALOG NUMBER: LD4D65D010-EU4DR6555659024-4LBDP1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	4919.3
2.5°	4940.3
5°	4904.6
7.5°	4978.7
10°	5019.3
12.5°	5009.5
15°	4931.2
17.5°	4739.7
20°	4416.7
22.5°	4036.4
25°	3629.5
27.5°	3170.3
30°	2655.0
32.5°	2188.1
35°	1774.2
37.5°	1365.3
40°	979.4
42.5°	639.6
45°	367.0
47.5°	194.3
50°	120.9
52.5°	83.9
55°	60.1
57.5°	43.3
60°	30.1
62.5°	19.6
65°	14.0
67.5°	12.6
70°	11.9
72.5°	9.1
75°	7.0
77.5°	6.3
80°	4.9
82.5°	3.5
85°	2.1
87.5°	1.4
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)