

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P740686

Luminaire Tested: LD4D05D010-EU4DR650210IC9050-4LBDP1MW

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P740686
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D05D010-EU4DR650210IC9050-4LBDP1MW
Description: 4 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 515.0 lumens
Efficiency: N/A
Efficacy: 68.7 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 7.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P740686

CATALOG NUMBER: LD4D05D010-EU4DR650210IC9050-4LBDP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P740686

CATALOG NUMBER: LD4D05D010-EU4DR650210IC9050-4LBDP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR	0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100	100	100													
	1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93	93	93	93	93	93													
	2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87	87	87	87	87	87													
	3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80	80	80	80	80	80													
	4	97	89	84	79	95	88	83	79	86	82	78	84	80	77	82	79	76	75	75	75	75	75	75													
	5	92	83	78	73	90	83	77	73	81	76	72	79	75	72	77	74	71	69	69	69	69	69	69													
	6	87	78	72	68	86	77	72	68	76	71	67	74	70	67	73	69	66	65	65	65	65	65	65													
	7	83	73	67	63	81	73	67	63	71	66	62	70	66	62	69	65	62	60	60	60	60	60	60													
	8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	57	57	57	57	57	57													
	9	75	65	59	55	74	65	59	55	64	58	55	63	58	55	62	58	54	53	53	53	53	53	53													
	10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50	50	50	50	50	50													

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	55406
5°	55442
10°	57404
15°	57496
20°	52939
25°	45100
30°	34518
35°	24396
40°	14406
45°	5841
50°	2125
55°	1181
60°	677
65°	362
70°	383
75°	296
80°	315
85°	251

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 5841 cd/sqm



TEST NUMBER: P740686

CATALOG NUMBER: LD4D05D010-EU4DR650210IC9050-4LBDP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	48.8	9.5
10°-20°	140.8	27.3
20°-30°	169.0	32.8
30°-40°	113.6	22.1
40°-50°	34.0	6.6
50°-60°	6.0	1.2
60°-70°	1.7	0.3
70°-80°	0.8	0.2
80°-90°	0.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	358.6	69.6
0°-40°	472.2	91.7
0°-60°	512.2	99.5
0°-90°	515.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	515.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	507	
5°	506	49
15°	508	141
25°	374	169
35°	183	114
45°	38	34
55°	6	6
65°	1	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P740686

CATALOG NUMBER: LD4D05D010-EU4DR650210IC9050-4LBDP1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	507.1
2.5°	509.2
5°	505.5
7.5°	513.2
10°	517.4
12.5°	516.3
15°	508.3
17.5°	488.6
20°	455.3
22.5°	416.0
25°	374.1
27.5°	326.8
30°	273.6
32.5°	225.5
35°	182.9
37.5°	140.7
40°	101.0
42.5°	65.9
45°	37.8
47.5°	20.1
50°	12.5
52.5°	8.7
55°	6.2
57.5°	4.5
60°	3.1
62.5°	2.0
65°	1.4
67.5°	1.3
70°	1.2
72.5°	0.9
75°	0.7
77.5°	0.6
80°	0.5
82.5°	0.3
85°	0.2
87.5°	0.2
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)