

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P752003

Luminaire Tested: LD4D65D010-EU4DR6555659030-4LBDP1MW

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P752003
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D65D010-EU4DR6555659030-4LBDP1MW
Description: 4 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5030.8 lumens
Efficiency: N/A
Efficacy: 69.1 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 72.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P752003
CATALOG NUMBER: LD4D65D010-EU4DR6555659030-4LBDP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P752003

CATALOG NUMBER: LD4D65D010-EU4DR6555659030-4LBDP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93																			
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87																			
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80																			
4	97	89	84	79	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	83	78	73	90	83	77	73	81	76	72	79	75	72	77	74	71	69																			
6	87	78	72	68	86	77	72	68	76	71	67	74	70	67	73	69	66	65																			
7	83	73	67	63	81	73	67	63	71	66	62	70	66	62	69	65	62	60																			
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	57																			
9	75	65	59	55	74	65	59	55	64	58	55	63	58	55	62	58	54	53																			
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	541190
5°	541634
10°	560711
15°	561639
20°	517077
25°	440572
30°	337273
35°	238275
40°	140647
45°	57094
50°	20704
55°	11525
60°	6621
65°	3645
70°	3833
75°	2955
80°	3083
85°	2633

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 57094 cd/sqm



TEST NUMBER: P752003

CATALOG NUMBER: LD4D65D010-EU4DR6555659030-4LBDP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	476.9	9.5
10°-20°	1375.8	27.3
20°-30°	1650.7	32.8
30°-40°	1109.3	22.0
40°-50°	332.1	6.6
50°-60°	58.6	1.2
60°-70°	16.7	0.3
70°-80°	8.2	0.2
80°-90°	2.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3503.4	69.6
0°-40°	4612.7	91.7
0°-60°	5003.4	99.5
0°-90°	5030.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5030.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4953	
5°	4938	477
15°	4965	1376
25°	3654	1651
35°	1786	1109
45°	370	332
55°	60	59
65°	14	17
75°	7	8
85°	2	3
90°	0	



TEST NUMBER: P752003

CATALOG NUMBER: LD4D65D010-EU4DR6555659030-4LBDP1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	4953.2
2.5°	4974.3
5°	4938.4
7.5°	5013.0
10°	5053.9
12.5°	5044.0
15°	4965.2
17.5°	4772.3
20°	4447.1
22.5°	4064.2
25°	3654.5
27.5°	3192.1
30°	2673.3
32.5°	2203.1
35°	1786.4
37.5°	1374.7
40°	986.1
42.5°	644.1
45°	369.5
47.5°	195.7
50°	121.8
52.5°	84.5
55°	60.5
57.5°	43.6
60°	30.3
62.5°	19.7
65°	14.1
67.5°	12.7
70°	12.0
72.5°	9.2
75°	7.0
77.5°	6.3
80°	4.9
82.5°	3.5
85°	2.1
87.5°	1.4
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)