

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P752080

Luminaire Tested: LD4D65D010-EU4DR7055659030-4LBDP1LI

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P752080
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D65D010-EU4DR7055659030-4LBDP1LI
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7052.8 lumens
Efficiency: N/A
Efficacy: 96.9 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 72.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P752080
CATALOG NUMBER: LD4D65D010-EU4DR7055659030-4LBDP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P752080
 CATALOG NUMBER: LD4D65D010-EU4DR7055659030-4LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	866372
5°	840628
10°	817197
15°	806476
20°	753088
25°	565757
30°	399938
35°	141666
40°	74496
45°	79345
50°	82151
55°	83701
60°	84218
65°	82446
70°	77820
75°	72061
80°	63990
85°	51900

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 84249 cd/sqm



TEST NUMBER: P752080

CATALOG NUMBER: LD4D65D010-EU4DR7055659030-4LBDP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	722.9	10.3
10°-20°	1983.0	28.1
20°-30°	2184.0	31.0
30°-40°	834.4	11.8
40°-50°	394.0	5.6
50°-60°	391.7	5.6
60°-70°	313.6	4.4
70°-80°	180.2	2.6
80°-90°	49.0	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4889.9	69.3
0°-40°	5724.3	81.2
0°-60°	6510.0	92.3
0°-90°	7052.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7052.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7929	
5°	7664	723
15°	7130	1983
25°	4693	2184
35°	1062	834
45°	514	394
55°	439	392
65°	319	314
75°	171	180
85°	41	49
90°	0	



TEST NUMBER: P752080

CATALOG NUMBER: LD4D65D010-EU4DR7055659030-4LBDP1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	7929.4
2.5°	7846.6
5°	7664.5
7.5°	7512.6
10°	7365.7
12.5°	7241.4
15°	7129.7
17.5°	6859.8
20°	6476.9
22.5°	5650.8
25°	4692.9
27.5°	4085.2
30°	3170.0
32.5°	2047.6
35°	1062.1
37.5°	573.7
40°	522.3
42.5°	518.5
45°	513.5
47.5°	502.2
50°	483.3
52.5°	462.0
55°	439.4
57.5°	414.3
60°	385.4
62.5°	352.8
65°	318.9
67.5°	281.2
70°	243.6
72.5°	205.9
75°	170.7
77.5°	134.3
80°	101.7
82.5°	71.6
85°	41.4
87.5°	16.3
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)