

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P749648

Luminaire Tested: LD4D50D010-EU4DR6540509027-4LBDP1H

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P749648
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D50D010-EU4DR6540509027-4LBDP1H
Description: 4 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4116.3 lumens
Efficiency: N/A
Efficacy: 87.6 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 47
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P749648

CATALOG NUMBER: LD4D50D010-EU4DR6540509027-4LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P749648

CATALOG NUMBER: LD4D50D010-EU4DR6540509027-4LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93		
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87		
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80		
4	97	89	84	79	95	88	83	79	86	82	78	84	80	77	82	79	76	75		
5	92	83	78	73	90	83	77	73	81	76	72	79	75	72	77	74	71	69		
6	87	78	72	68	86	77	72	68	76	71	67	74	70	67	73	69	66	65		
7	83	73	67	63	81	73	67	63	71	66	62	70	66	62	69	65	62	60		
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	57		
9	75	65	59	55	74	65	59	55	64	58	55	63	58	55	62	58	54	53		
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	442801
5°	443165
10°	458763
15°	459530
20°	423070
25°	360474
30°	275957
35°	194966
40°	115088
45°	46726
50°	16930
55°	9429
60°	5419
65°	2973
70°	3131
75°	2448
80°	2517
85°	2131

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 46726 cd/sqm



TEST NUMBER: P749648

CATALOG NUMBER: LD4D50D010-EU4DR6540509027-4LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	390.2	9.5
10°-20°	1125.7	27.3
20°-30°	1350.6	32.8
30°-40°	907.6	22.1
40°-50°	271.7	6.6
50°-60°	47.9	1.2
60°-70°	13.6	0.3
70°-80°	6.7	0.2
80°-90°	2.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2866.5	69.6
0°-40°	3774.1	91.7
0°-60°	4093.8	99.5
0°-90°	4116.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4116.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4053	
5°	4041	390
15°	4062	1126
25°	2990	1351
35°	1462	908
45°	302	272
55°	50	48
65°	12	14
75°	6	7
85°	2	2
90°	0	



TEST NUMBER: P749648

CATALOG NUMBER: LD4D50D010-EU4DR6540509027-4LBDP1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	4052.7
2.5°	4070.0
5°	4040.6
7.5°	4101.6
10°	4135.0
12.5°	4127.0
15°	4062.5
17.5°	3904.7
20°	3638.6
22.5°	3325.3
25°	2990.1
27.5°	2611.8
30°	2187.3
32.5°	1802.6
35°	1461.7
37.5°	1124.8
40°	806.9
42.5°	527.0
45°	302.4
47.5°	160.1
50°	99.6
52.5°	69.1
55°	49.5
57.5°	35.7
60°	24.8
62.5°	16.1
65°	11.5
67.5°	10.4
70°	9.8
72.5°	7.5
75°	5.8
77.5°	5.2
80°	4.0
82.5°	2.9
85°	1.7
87.5°	1.2
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)