

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P751394

Luminaire Tested: LD4D65D010-EU4DR2555659035-4LBS1H

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P751394
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-4)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D65D010-EU4DR2555659035-4LBS1H
Description: 4 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 25° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6324.6 lumens
Efficiency: N/A
Efficacy: 86.9 lumens/watt
Spacing Criteria (0/90/45): 0.42 / 0.42 / 0.45
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 72.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P751394
CATALOG NUMBER: LD4D65D010-EU4DR2555659035-4LBS1H

Luminous Intensity Polar Plot





TEST NUMBER: P751394

CATALOG NUMBER: LD4D65D010-EU4DR2555659035-4LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|----|----|----|----|----|----|----|----|----|---|--|--|--|--|--|--|---|--|--|--|--|--|--|--|--|
| RF | 20 | | | | | | | | | 20 | | | | | | | | | 20 | | | | | | | | | 20 | | | | | | | | | | | | | | | | | |
| RC | 80 | | | | | | | | | 50 | | | | | | | | | 30 | | | | | | | | | 10 | | | | | | | | | 0 | | | | | | | | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 | | | | | | | | | | | | | | | |
| RCR | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 1 | 115 | 113 | 111 | 109 | 112 | 110 | 109 | 107 | 106 | 105 | 104 | 103 | 102 | 101 | 99 | 99 | 98 | 96 | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 2 | 111 | 107 | 104 | 101 | 109 | 105 | 102 | 100 | 102 | 100 | 98 | 99 | 97 | 96 | 97 | 95 | 94 | 92 | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 3 | 107 | 102 | 98 | 95 | 105 | 101 | 97 | 94 | 98 | 95 | 93 | 96 | 93 | 91 | 94 | 92 | 90 | 89 | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 4 | 103 | 97 | 93 | 90 | 102 | 96 | 93 | 90 | 94 | 91 | 89 | 93 | 90 | 88 | 91 | 89 | 87 | 85 | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 5 | 100 | 93 | 89 | 86 | 98 | 93 | 89 | 86 | 91 | 87 | 85 | 89 | 86 | 84 | 88 | 85 | 83 | 82 | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 6 | 97 | 90 | 85 | 82 | 95 | 89 | 85 | 82 | 88 | 84 | 81 | 87 | 83 | 81 | 85 | 83 | 80 | 79 | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 7 | 93 | 87 | 82 | 79 | 92 | 86 | 82 | 79 | 85 | 81 | 78 | 84 | 80 | 78 | 83 | 80 | 78 | 77 | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 8 | 91 | 84 | 79 | 76 | 90 | 83 | 79 | 76 | 82 | 78 | 76 | 81 | 78 | 75 | 80 | 77 | 75 | 74 | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 9 | 88 | 81 | 76 | 73 | 87 | 80 | 76 | 73 | 80 | 76 | 73 | 79 | 75 | 73 | 78 | 75 | 73 | 72 | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 10 | 85 | 78 | 74 | 71 | 85 | 78 | 74 | 71 | 77 | 73 | 71 | 76 | 73 | 71 | 76 | 73 | 70 | 69 | | | | | | | | | | | | | | | | | | | | | | | | | | | |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|---------|
| | 0° |
| 0° | 2620925 |
| 5° | 2441062 |
| 10° | 1741280 |
| 15° | 1025546 |
| 20° | 638105 |
| 25° | 350191 |
| 30° | 160152 |
| 35° | 60649 |
| 40° | 27470 |
| 45° | 16518 |
| 50° | 6850 |
| 55° | 4419 |
| 60° | 3081 |
| 65° | 2094 |
| 70° | 319 |
| 75° | 0 |
| 80° | 0 |
| 85° | 0 |

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 16518 cd/sqm



TEST NUMBER: P751394

CATALOG NUMBER: LD4D65D010-EU4DR2555659035-4LBS1H

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 1912.8 | 30.2 |
| 10°-20° | 2590.7 | 41.0 |
| 20°-30° | 1371.0 | 21.7 |
| 30°-40° | 338.4 | 5.4 |
| 40°-50° | 82.6 | 1.3 |
| 50°-60° | 21.7 | 0.3 |
| 60°-70° | 7.3 | 0.1 |
| 70°-80° | 0.1 | 0.0 |
| 80°-90° | 0.0 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 5874.5 | 92.9 |
| 0°-40° | 6212.9 | 98.2 |
| 0°-60° | 6317.1 | 99.9 |
| 0°-90° | 6324.6 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 6324.6 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|-------|------|
| 0° | 23988 | |
| 5° | 22257 | ### |
| 15° | 9066 | 2591 |
| 25° | 2905 | 1371 |
| 35° | 455 | 338 |
| 45° | 107 | 83 |
| 55° | 23 | 22 |
| 65° | 8 | 7 |
| 75° | 0 | 0 |
| 85° | 0 | 0 |
| 90° | 0 | |



TEST NUMBER: P751394

CATALOG NUMBER: LD4D65D010-EU4DR2555659035-4LBS1H

CANDELA DISTRIBUTION (FULL):

| 0° | |
|-------|---------|
| 0° | 23987.8 |
| 2.5° | 23593.6 |
| 5° | 22256.6 |
| 7.5° | 19570.6 |
| 10° | 15694.8 |
| 12.5° | 11864.3 |
| 15° | 9066.4 |
| 17.5° | 7066.0 |
| 20° | 5488.0 |
| 22.5° | 4115.8 |
| 25° | 2904.8 |
| 27.5° | 1948.0 |
| 30° | 1269.4 |
| 32.5° | 772.3 |
| 35° | 454.7 |
| 37.5° | 278.3 |
| 40° | 192.6 |
| 42.5° | 147.2 |
| 45° | 106.9 |
| 47.5° | 64.5 |
| 50° | 40.3 |
| 52.5° | 29.2 |
| 55° | 23.2 |
| 57.5° | 18.1 |
| 60° | 14.1 |
| 62.5° | 11.1 |
| 65° | 8.1 |
| 67.5° | 3.0 |
| 70° | 1.0 |
| 72.5° | 0.0 |
| 75° | 0.0 |
| 77.5° | 0.0 |
| 80° | 0.0 |
| 82.5° | 0.0 |
| 85° | 0.0 |
| 87.5° | 0.0 |
| 90° | 0.0 |

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)