

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P751948

Luminaire Tested: LD4D65D010-EU4DR6055659040-4LBDP1B

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P751948  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D65D010-EU4DR6055659040-4LBDP1B  
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 60° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5558.7 lumens  
Efficiency: N/A  
Efficacy: 76.4 lumens/watt  
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct


Input Watts (W): 72.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



Downlight

TEST NUMBER: P751948  
CATALOG NUMBER: LD4D65D010-EU4DR6055659040-4LBDP1B

### Luminous Intensity Polar Plot





TEST NUMBER: P751948  
 CATALOG NUMBER: LD4D65D010-EU4DR6055659040-4LBDP1B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93																			
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86																			
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80																			
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70																			
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66																			
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62																			
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59																			
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55																			
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	721296
5°	739033
10°	747955
15°	712534
20°	628234
25°	508131
30°	343707
35°	172237
40°	27941
45°	27350
50°	27894
55°	28307
60°	29107
65°	29757
70°	30476
75°	30817
80°	29762
85°	24822

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 75°  
 Luminance: 30817 cd/sqm



TEST NUMBER: P751948

CATALOG NUMBER: LD4D65D010-EU4DR6055659040-4LBDP1B

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	644.0	11.6
10°-20°	1742.4	31.3
20°-30°	1874.7	33.7
30°-40°	814.9	14.7
40°-50°	136.9	2.5
50°-60°	133.1	2.4
60°-70°	113.8	2.0
70°-80°	76.2	1.4
80°-90°	22.8	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4261.0	76.7
0°-40°	5075.9	91.3
0°-60°	5345.9	96.2
0°-90°	5558.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5558.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	6602	
5°	6738	644
15°	6299	1742
25°	4215	1875
35°	1291	815
45°	177	137
55°	149	133
65°	115	114
75°	73	76
85°	20	23
90°	0	



TEST NUMBER: P751948

CATALOG NUMBER: LD4D65D010-EU4DR6055659040-4LBDP1B

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	6601.6
2.5°	6787.2
5°	6738.2
7.5°	6753.6
10°	6741.6
12.5°	6602.4
15°	6299.2
17.5°	5891.9
20°	5403.1
22.5°	4879.9
25°	4214.9
27.5°	3371.2
30°	2724.3
32.5°	2099.7
35°	1291.3
37.5°	552.4
40°	195.9
42.5°	180.4
45°	177.0
47.5°	171.0
50°	164.1
52.5°	156.4
55°	148.6
57.5°	140.9
60°	133.2
62.5°	124.6
65°	115.1
67.5°	105.7
70°	95.4
72.5°	84.2
75°	73.0
77.5°	60.1
80°	47.3
82.5°	33.5
85°	19.8
87.5°	6.9
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)