

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P751964

Luminaire Tested: LD4D65D010-EU4DR6055659050-4LBDP1MW

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P751964  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D65D010-EU4DR6055659050-4LBDP1MW  
Description: 4 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 60° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6438.2 lumens  
Efficiency: N/A  
Efficacy: 88.4 lumens/watt  
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct


Input Watts (W): 72.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



Downlight

TEST NUMBER: P751964  
CATALOG NUMBER: LD4D65D010-EU4DR6055659050-4LBDP1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P751964

CATALOG NUMBER: LD4D65D010-EU4DR6055659050-4LBDP1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93		
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86		
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80		
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75		
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70		
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66		
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62		
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59		
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55		
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53		

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	835430
5°	855972
10°	866313
15°	825276
20°	727636
25°	588530
30°	398096
35°	199487
40°	32363
45°	31676
50°	32313
55°	32783
60°	33696
65°	34462
70°	35300
75°	35714
80°	34418
85°	28708

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 75°  
 Luminance: 35714 cd/sqm



TEST NUMBER: P751964

CATALOG NUMBER: LD4D65D010-EU4DR6055659050-4LBDP1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	745.9	11.6
10°-20°	2018.1	31.3
20°-30°	2171.3	33.7
30°-40°	943.8	14.7
40°-50°	158.5	2.5
50°-60°	154.1	2.4
60°-70°	131.8	2.0
70°-80°	88.2	1.4
80°-90°	26.4	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4935.3	76.7
0°-40°	5879.1	91.3
0°-60°	6191.8	96.2
0°-90°	6438.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6438.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	7646	
5°	7804	746
15°	7296	2018
25°	4882	2171
35°	1496	944
45°	205	159
55°	172	154
65°	133	132
75°	85	88
85°	23	26
90°	0	



TEST NUMBER: P751964

CATALOG NUMBER: LD4D65D010-EU4DR6055659050-4LBDP1MW

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	7646.2
2.5°	7861.1
5°	7804.4
7.5°	7822.3
10°	7808.4
12.5°	7647.2
15°	7295.9
17.5°	6824.2
20°	6258.0
22.5°	5652.0
25°	4881.8
27.5°	3904.7
30°	3155.4
32.5°	2432.0
35°	1495.6
37.5°	639.8
40°	226.9
42.5°	209.0
45°	205.0
47.5°	198.0
50°	190.1
52.5°	181.1
55°	172.1
57.5°	163.2
60°	154.2
62.5°	144.3
65°	133.3
67.5°	122.4
70°	110.5
72.5°	97.5
75°	84.6
77.5°	69.7
80°	54.7
82.5°	38.8
85°	22.9
87.5°	8.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)