

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P749596

Luminaire Tested: LD4D50D010-EU4DR6040509035-4LBDP1H

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P749596
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D50D010-EU4DR6040509035-4LBDP1H
Description: 4 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4904.3 lumens
Efficiency: N/A
Efficacy: 104.3 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 47
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P749596
CATALOG NUMBER: LD4D50D010-EU4DR6040509035-4LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P749596

CATALOG NUMBER: LD4D50D010-EU4DR6040509035-4LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93																			
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86																			
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80																			
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70																			
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66																			
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62																			
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59																			
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55																			
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	636389
5°	652036
10°	659920
15°	628660
20°	554284
25°	448323
30°	303246
35°	151963
40°	24646
45°	24120
50°	24613
55°	24973
60°	25676
65°	26267
70°	26866
75°	27187
80°	26238
85°	21813

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 27187 cd/sqm



TEST NUMBER: P749596

CATALOG NUMBER: LD4D50D010-EU4DR6040509035-4LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	568.2	11.6
10°-20°	1537.3	31.3
20°-30°	1654.0	33.7
30°-40°	719.0	14.7
40°-50°	120.7	2.5
50°-60°	117.4	2.4
60°-70°	100.4	2.0
70°-80°	67.2	1.4
80°-90°	20.1	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3759.5	76.7
0°-40°	4478.4	91.3
0°-60°	4716.6	96.2
0°-90°	4904.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4904.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5824	
5°	5945	568
15°	5558	1537
25°	3719	1654
35°	1139	719
45°	156	121
55°	131	117
65°	102	100
75°	64	67
85°	17	20
90°	0	



TEST NUMBER: P749596
CATALOG NUMBER: LD4D50D010-EU4DR6040509035-4LBDP1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	5824.5
2.5°	5988.2
5°	5945.0
7.5°	5958.7
10°	5948.1
12.5°	5825.3
15°	5557.7
17.5°	5198.4
20°	4767.1
22.5°	4305.5
25°	3718.8
27.5°	2974.4
30°	2403.6
32.5°	1852.6
35°	1139.3
37.5°	487.4
40°	172.8
42.5°	159.2
45°	156.1
47.5°	150.8
50°	144.8
52.5°	138.0
55°	131.1
57.5°	124.3
60°	117.5
62.5°	109.9
65°	101.6
67.5°	93.2
70°	84.1
72.5°	74.3
75°	64.4
77.5°	53.1
80°	41.7
82.5°	29.6
85°	17.4
87.5°	6.1
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)