

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P749609

Luminaire Tested: LD4D50D010-EU4DR6040509040-4LBDP1H

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P749609
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D50D010-EU4DR6040509040-4LBDP1H
Description: 4 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5133.5 lumens
Efficiency: N/A
Efficacy: 109.2 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 47
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P749609
CATALOG NUMBER: LD4D50D010-EU4DR6040509040-4LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P749609

CATALOG NUMBER: LD4D50D010-EU4DR6040509040-4LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93	93	93	93
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86	86	86	86
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80	80	80	80
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75	75	75	75
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70	70	70	70
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66	66	66	66
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62	62	62	62
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59	59	59	59
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55	55	55	55
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53	53	53	53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	666141
5°	682527
10°	690763
15°	658047
20°	580202
25°	469276
30°	317427
35°	159059
40°	25802
45°	25248
50°	25752
55°	26154
60°	26878
65°	27482
70°	28144
75°	28453
80°	27433
85°	22816

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 28453 cd/sqm



TEST NUMBER: P749609

CATALOG NUMBER: LD4D50D010-EU4DR6040509040-4LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	594.8	11.6
10°-20°	1609.2	31.3
20°-30°	1731.3	33.7
30°-40°	752.6	14.7
40°-50°	126.4	2.5
50°-60°	122.9	2.4
60°-70°	105.1	2.0
70°-80°	70.3	1.4
80°-90°	21.0	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3935.2	76.7
0°-40°	4687.8	91.3
0°-60°	4937.1	96.2
0°-90°	5133.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5133.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6097	
5°	6223	595
15°	5818	1609
25°	3893	1731
35°	1192	753
45°	163	126
55°	137	123
65°	106	105
75°	67	70
85°	18	21
90°	0	



TEST NUMBER: P749609

CATALOG NUMBER: LD4D50D010-EU4DR6040509040-4LBDP1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	6096.8
2.5°	6268.2
5°	6223.0
7.5°	6237.3
10°	6226.1
12.5°	6097.6
15°	5817.5
17.5°	5441.4
20°	4990.0
22.5°	4506.8
25°	3892.6
27.5°	3113.5
30°	2516.0
32.5°	1939.2
35°	1192.5
37.5°	510.2
40°	180.9
42.5°	166.6
45°	163.4
47.5°	157.9
50°	151.5
52.5°	144.4
55°	137.3
57.5°	130.1
60°	123.0
62.5°	115.0
65°	106.3
67.5°	97.6
70°	88.1
72.5°	77.8
75°	67.4
77.5°	55.5
80°	43.6
82.5°	30.9
85°	18.2
87.5°	6.3
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)