

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P752045

Luminaire Tested: LD4D65D010-EU4DR6555659050-4LBS1LI

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P752045  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D65D010-EU4DR6555659050-4LBS1LI  
Description: 4 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 65° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6865.7 lumens  
Efficiency: N/A  
Efficacy: 94.3 lumens/watt  
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96  
Luminous Opening: Circular (Dia: 0.48' x H: 0')  
CIE Type: Direct


Input Watts (W): 72.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



Downlight

TEST NUMBER: P752045  
CATALOG NUMBER: LD4D65D010-EU4DR6555659050-4LBS1LI

### Luminous Intensity Polar Plot





TEST NUMBER: P752045

CATALOG NUMBER: LD4D65D010-EU4DR6555659050-4LBS1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93			93																
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85			85																
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78			78																
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72			72																
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66			66																
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61			61																
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56			56																
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52			52																
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49			49																
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46			46																

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	364084
5°	363165
10°	362851
15°	351665
20°	320152
25°	278993
30°	232044
35°	183856
40°	132697
45°	83834
50°	43695
55°	23226
60°	12195
65°	6716
70°	2818
75°	3091
80°	2153
85°	1809

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 83834 cd/sqm



TEST NUMBER: P752045

CATALOG NUMBER: LD4D65D010-EU4DR6555659050-4LBS1LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	589.5	8.6
10°-20°	1614.4	23.5
20°-30°	1973.3	28.7
30°-40°	1601.1	23.3
40°-50°	797.8	11.6
50°-60°	222.5	3.2
60°-70°	50.6	0.7
70°-80°	13.2	0.2
80°-90°	3.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4177.2	60.8
0°-40°	5778.2	84.2
0°-60°	6798.6	99.0
0°-90°	6865.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6865.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	6234	
5°	6194	590
15°	5816	1614
25°	4329	1973
35°	2579	1601
45°	1015	798
55°	228	223
65°	49	51
75°	14	13
85°	3	3
90°	0	



TEST NUMBER: P752045

CATALOG NUMBER: LD4D65D010-EU4DR6555659050-4LBS1LI

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	6233.9
2.5°	6229.3
5°	6194.5
7.5°	6174.3
10°	6118.4
12.5°	6004.9
15°	5816.1
17.5°	5521.2
20°	5151.1
22.5°	4751.7
25°	4329.4
27.5°	3877.7
30°	3440.8
32.5°	3009.3
35°	2578.7
37.5°	2149.1
40°	1740.5
42.5°	1357.6
45°	1015.0
47.5°	707.2
50°	480.9
52.5°	331.6
55°	228.1
57.5°	153.9
60°	104.4
62.5°	72.4
65°	48.6
67.5°	24.7
70°	16.5
72.5°	15.6
75°	13.7
77.5°	9.2
80°	6.4
82.5°	4.6
85°	2.7
87.5°	1.8
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)