

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P752912

Luminaire Tested: LD4D75BD010-EU4DR2570959024-4LBDP1LI

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P752912
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-4)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D75BD010-EU4DR2570959024-4LBDP1LI
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 25° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5763.4 lumens
Efficiency: N/A
Efficacy: 79.6 lumens/watt
Spacing Criteria (0/90/45): 0.42 / 0.42 / 0.45
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 72.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P752912

CATALOG NUMBER: LD4D75BD010-EU4DR2570959024-4LBDP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P752912

CATALOG NUMBER: LD4D75BD010-EU4DR2570959024-4LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96			
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92			
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89			
4	103	97	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85			
5	100	93	89	86	98	93	89	86	91	87	85	89	86	84	88	85	83	82			
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79			
7	93	87	82	79	92	86	82	79	85	81	78	84	80	78	83	80	78	77			
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74			
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72			
10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70	69			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2388364
5°	2224459
10°	1586765
15°	934545
20°	581492
25°	319124
30°	145946
35°	55274
40°	25032
45°	15050
50°	6255
55°	4019
60°	2819
65°	1913
70°	288
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 15050 cd/sqm



TEST NUMBER: P752912

CATALOG NUMBER: LD4D75BD010-EU4DR2570959024-4LBDP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1743.0	30.2
10°-20°	2360.8	41.0
20°-30°	1249.3	21.7
30°-40°	308.4	5.4
40°-50°	75.2	1.3
50°-60°	19.8	0.3
60°-70°	6.7	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5353.2	92.9
0°-40°	5661.6	98.2
0°-60°	5756.6	99.9
0°-90°	5763.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5763.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	21859	
5°	20282	###
15°	8262	2361
25°	2647	1249
35°	414	308
45°	97	75
55°	21	20
65°	7	7
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P752912

CATALOG NUMBER: LD4D75BD010-EU4DR2570959024-4LBDP1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	21859.3
2.5°	21500.0
5°	20281.7
7.5°	17834.0
10°	14302.1
12.5°	10811.6
15°	8261.9
17.5°	6439.0
20°	5001.1
22.5°	3750.6
25°	2647.1
27.5°	1775.1
30°	1156.8
32.5°	703.8
35°	414.4
37.5°	253.6
40°	175.5
42.5°	134.1
45°	97.4
47.5°	58.8
50°	36.8
52.5°	26.6
55°	21.1
57.5°	16.5
60°	12.9
62.5°	10.1
65°	7.4
67.5°	2.8
70°	0.9
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)