

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P749610

Luminaire Tested: LD4D50D010-EU4DR6040509040-4LBDP1LI

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P749610  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D50D010-EU4DR6040509040-4LBDP1LI  
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 60° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5390.3 lumens  
Efficiency: N/A  
Efficacy: 114.7 lumens/watt  
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 47  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



Downlight

TEST NUMBER: P749610  
CATALOG NUMBER: LD4D50D010-EU4DR6040509040-4LBDP1LI

### Luminous Intensity Polar Plot





TEST NUMBER: P749610

CATALOG NUMBER: LD4D50D010-EU4DR6040509040-4LBDP1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93	93	93	93
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86	86	86	86
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80	80	80	80
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75	75	75	75
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70	70	70	70
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66	66	66	66
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62	62	62	62
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59	59	59	59
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55	55	55	55
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53	53	53	53

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	699455
5°	716648
10°	725300
15°	690952
20°	609212
25°	492748
30°	333299
35°	167022
40°	27100
45°	26515
50°	27044
55°	27450
60°	28211
65°	28852
70°	29550
75°	29888
80°	28818
85°	24070

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 75°  
 Luminance: 29888 cd/sqm



TEST NUMBER: P749610

CATALOG NUMBER: LD4D50D010-EU4DR6040509040-4LBDP1LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	624.5	11.6
10°-20°	1689.6	31.3
20°-30°	1817.9	33.7
30°-40°	790.2	14.7
40°-50°	132.7	2.5
50°-60°	129.0	2.4
60°-70°	110.4	2.0
70°-80°	73.8	1.4
80°-90°	22.1	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4132.0	76.7
0°-40°	4922.2	91.3
0°-60°	5184.0	96.2
0°-90°	5390.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5390.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	6402	
5°	6534	624
15°	6108	1690
25°	4087	1818
35°	1252	790
45°	172	133
55°	144	129
65°	112	110
75°	71	74
85°	19	22
90°	0	



TEST NUMBER: P749610

CATALOG NUMBER: LD4D50D010-EU4DR6040509040-4LBDP1LI

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	6401.7
2.5°	6581.6
5°	6534.1
7.5°	6549.1
10°	6537.4
12.5°	6402.5
15°	6108.4
17.5°	5713.5
20°	5239.5
22.5°	4732.1
25°	4087.3
27.5°	3269.1
30°	2641.8
32.5°	2036.1
35°	1252.2
37.5°	535.7
40°	190.0
42.5°	175.0
45°	171.6
47.5°	165.8
50°	159.1
52.5°	151.6
55°	144.1
57.5°	136.6
60°	129.1
62.5°	120.8
65°	111.6
67.5°	102.5
70°	92.5
72.5°	81.6
75°	70.8
77.5°	58.3
80°	45.8
82.5°	32.5
85°	19.2
87.5°	6.7
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)