

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P750105

Luminaire Tested: LD4D55D010-EU4DR4555659024-4LBDP1MW

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P750105
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-36)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D55D010-EU4DR4555659024-4LBDP1MW
Description: 4 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 45° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4544.3 lumens
Efficiency: N/A
Efficacy: 78.1 lumens/watt
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.69
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 58.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P750105

CATALOG NUMBER: LD4D55D010-EU4DR4555659024-4LBDP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P750105

CATALOG NUMBER: LD4D55D010-EU4DR4555659024-4LBDP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						100													
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	98	98	97	95						95													
2	109	105	102	99	107	103	100	98	100	98	95	97	95	93	95	93	91	90						90													
3	105	99	95	91	103	98	94	91	95	92	89	93	90	88	91	89	87	85						85													
4	100	94	89	85	99	93	88	85	91	87	84	89	86	83	87	84	82	81						81													
5	96	89	84	80	95	88	83	80	86	82	79	85	81	79	83	80	78	77						77													
6	92	85	80	76	91	84	79	76	83	78	75	81	77	75	80	77	74	73						73													
7	89	81	75	72	87	80	75	72	79	74	71	78	74	71	77	73	71	69						69													
8	85	77	72	68	84	76	71	68	75	71	68	74	70	67	73	70	67	66						66													
9	82	73	68	65	81	73	68	65	72	68	65	71	67	64	71	67	64	63						63													
10	79	70	65	62	78	70	65	62	69	65	62	68	64	61	68	64	61	60						60													

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	877593
5°	852605
10°	815710
15°	746548
20°	592271
25°	369757
30°	203804
35°	91514
40°	36043
45°	16982
50°	8057
55°	4210
60°	2076
65°	491
70°	192
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 16982 cd/sqm



TEST NUMBER: P750105

CATALOG NUMBER: LD4D55D010-EU4DR4555659024-4LBDP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	730.4	16.1
10°-20°	1797.6	39.6
20°-30°	1423.5	31.3
30°-40°	474.0	10.4
40°-50°	94.1	2.1
50°-60°	21.4	0.5
60°-70°	3.1	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3951.6	87.0
0°-40°	4425.6	97.4
0°-60°	4541.1	99.9
0°-90°	4544.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4544.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8032	
5°	7774	730
15°	6600	1798
25°	3067	1424
35°	686	474
45°	110	94
55°	22	21
65°	2	3
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P750105

CATALOG NUMBER: LD4D55D010-EU4DR4555659024-4LBDP1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	8032.1
2.5°	7979.6
5°	7773.7
7.5°	7603.7
10°	7352.3
12.5°	7017.5
15°	6599.9
17.5°	5971.9
20°	5093.8
22.5°	4047.6
25°	3067.1
27.5°	2245.9
30°	1615.4
32.5°	1098.6
35°	686.1
37.5°	406.8
40°	252.7
42.5°	166.2
45°	109.9
47.5°	70.8
50°	47.4
52.5°	31.6
55°	22.1
57.5°	14.5
60°	9.5
62.5°	5.1
65°	1.9
67.5°	0.6
70°	0.6
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)