

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P750492

Luminaire Tested: LD4D55D010-EU4DR7055659024-4LBDP1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P750492
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D55D010-EU4DR7055659024-4LBDP1B
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2753.6 lumens
Efficiency: N/A
Efficacy: 47.3 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 58.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P750492

CATALOG NUMBER: LD4D55D010-EU4DR7055659024-4LBDP1B

Luminous Intensity Polar Plot





TEST NUMBER: P750492

CATALOG NUMBER: LD4D55D010-EU4DR7055659024-4LBDP1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	338249
5°	328190
10°	319048
15°	314856
20°	294019
25°	220883
30°	156140
35°	55314
40°	29082
45°	30981
50°	32075
55°	32688
60°	32887
65°	32187
70°	30380
75°	28157
80°	24980
85°	20309

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 60°
 Luminance: 32887 cd/sqm



TEST NUMBER: P750492

CATALOG NUMBER: LD4D55D010-EU4DR7055659024-4LBDP1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	282.2	10.2
10°-20°	774.2	28.1
20°-30°	852.7	31.0
30°-40°	325.8	11.8
40°-50°	153.8	5.6
50°-60°	152.9	5.6
60°-70°	122.4	4.4
70°-80°	70.4	2.6
80°-90°	19.1	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1909.1	69.3
0°-40°	2234.9	81.2
0°-60°	2541.6	92.3
0°-90°	2753.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2753.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3096	
5°	2992	282
15°	2784	774
25°	1832	853
35°	415	326
45°	200	154
55°	172	153
65°	124	122
75°	67	70
85°	16	19
90°	0	



TEST NUMBER: P750492

CATALOG NUMBER: LD4D55D010-EU4DR7055659024-4LBDP1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	3095.8
2.5°	3063.4
5°	2992.3
7.5°	2933.0
10°	2875.7
12.5°	2827.2
15°	2783.5
17.5°	2678.2
20°	2528.7
22.5°	2206.2
25°	1832.2
27.5°	1594.9
30°	1237.6
32.5°	799.4
35°	414.7
37.5°	224.0
40°	203.9
42.5°	202.4
45°	200.5
47.5°	196.1
50°	188.7
52.5°	180.4
55°	171.6
57.5°	161.7
60°	150.5
62.5°	137.7
65°	124.5
67.5°	109.8
70°	95.1
72.5°	80.4
75°	66.7
77.5°	52.4
80°	39.7
82.5°	27.9
85°	16.2
87.5°	6.4
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)