

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P753071

Luminaire Tested: LD4D75BD010-EU4DR3570959024-4LBS1H

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P753071
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-20)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D75BD010-EU4DR3570959024-4LBS1H
Description: 4 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 35° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6176.5 lumens
Efficiency: N/A
Efficacy: 85.3 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.54
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 72.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P753071

CATALOG NUMBER: LD4D75BD010-EU4DR3570959024-4LBS1H

Luminous Intensity Polar Plot





TEST NUMBER: P753071

CATALOG NUMBER: LD4D75BD010-EU4DR3570959024-4LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	115	112	110	108		112	110	108	107		106	105	103		103	101	100		99	98	98
2	110	106	103	101		108	105	102	99		102	99	97		99	97	95		96	95	93
3	106	101	97	94		105	100	96	93		97	95	92		95	93	91		93	91	89
4	103	97	92	89		101	96	92	89		94	90	88		92	89	87		90	88	86
5	99	93	88	85		98	92	87	84		90	86	84		89	85	83		87	84	82
6	96	89	84	81		94	88	84	81		87	83	80		85	82	80		84	81	79
7	93	85	81	78		91	85	80	77		84	80	77		83	79	77		82	79	76
8	90	82	78	74		88	82	77	74		81	77	74		80	76	74		79	76	73
9	87	79	75	72		86	79	75	72		78	74	71		77	74	71		77	73	71
10	84	77	72	69		83	76	72	69		76	72	69		75	71	69		74	71	69

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1856843
5°	1813210
10°	1634183
15°	1268382
20°	719415
25°	279883
30°	104413
35°	57235
40°	37412
45°	22776
50°	14499
55°	10248
60°	7495
65°	4085
70°	288
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 22776 cd/sqm



TEST NUMBER: P753071

CATALOG NUMBER: LD4D75BD010-EU4DR3570959024-4LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1520.5	24.6
10°-20°	2968.6	48.1
20°-30°	1210.7	19.6
30°-40°	289.7	4.7
40°-50°	120.8	2.0
50°-60°	50.0	0.8
60°-70°	15.7	0.3
70°-80°	0.4	0.0
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5699.8	92.3
0°-40°	5989.5	97.0
0°-60°	6160.3	99.7
0°-90°	6176.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6176.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	16995	
5°	16532	###
15°	11213	2969
25°	2322	1211
35°	429	290
45°	147	121
55°	54	50
65°	16	16
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P753071

CATALOG NUMBER: LD4D75BD010-EU4DR3570959024-4LBS1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	16994.6
2.5°	16892.6
5°	16532.1
7.5°	15812.9
10°	14729.5
12.5°	13204.0
15°	11213.2
17.5°	8778.6
20°	6187.3
22.5°	3945.3
25°	2321.6
27.5°	1312.3
30°	827.6
32.5°	581.1
35°	429.1
37.5°	331.8
40°	262.3
42.5°	202.0
45°	147.4
47.5°	110.3
50°	85.3
52.5°	67.7
55°	53.8
57.5°	43.6
60°	34.3
62.5°	25.0
65°	15.8
67.5°	5.6
70°	0.9
72.5°	0.9
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.9
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)