

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P750508

Luminaire Tested: LD4D55D010-EU4DR7055659027-4LBDP1MW

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P750508
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D55D010-EU4DR7055659027-4LBDP1MW
Description: 4 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4187.5 lumens
Efficiency: N/A
Efficacy: 71.9 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 58.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P750508
CATALOG NUMBER: LD4D55D010-EU4DR7055659027-4LBDP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P750508

CATALOG NUMBER: LD4D55D010-EU4DR7055659027-4LBDP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	514389
5°	499101
10°	485190
15°	478827
20°	447127
25°	335905
30°	237452
35°	84111
40°	44229
45°	47113
50°	48784
55°	49699
60°	49998
65°	48940
70°	46193
75°	42806
80°	38004
85°	30839

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 50025 cd/sqm



TEST NUMBER: P750508

CATALOG NUMBER: LD4D55D010-EU4DR7055659027-4LBDP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	429.2	10.3
10°-20°	1177.3	28.1
20°-30°	1296.7	31.0
30°-40°	495.4	11.8
40°-50°	233.9	5.6
50°-60°	232.6	5.6
60°-70°	186.2	4.4
70°-80°	107.0	2.6
80°-90°	29.1	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2903.2	69.3
0°-40°	3398.6	81.2
0°-60°	3865.1	92.3
0°-90°	4187.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4187.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4708	
5°	4551	429
15°	4233	1177
25°	2786	1297
35°	631	495
45°	305	234
55°	261	233
65°	189	186
75°	101	107
85°	25	29
90°	0	



TEST NUMBER: P750508

CATALOG NUMBER: LD4D55D010-EU4DR7055659027-4LBDP1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	4707.9
2.5°	4658.7
5°	4550.6
7.5°	4460.4
10°	4373.2
12.5°	4299.4
15°	4233.1
17.5°	4072.8
20°	3845.5
22.5°	3355.0
25°	2786.3
27.5°	2425.5
30°	1882.1
32.5°	1215.7
35°	630.6
37.5°	340.6
40°	310.1
42.5°	307.8
45°	304.9
47.5°	298.2
50°	287.0
52.5°	274.3
55°	260.9
57.5°	246.0
60°	228.8
62.5°	209.5
65°	189.3
67.5°	167.0
70°	144.6
72.5°	122.2
75°	101.4
77.5°	79.8
80°	60.4
82.5°	42.5
85°	24.6
87.5°	9.7
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)