

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P753460

Luminaire Tested: LD4D75BD010-EU4DR6070959024-4LBS1B

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P753460
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-60)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D75BD010-EU4DR6070959024-4LBS1B
Description: 4 INCH ROUND SHALLOW SPECULAR BLACK TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6076.6 lumens
Efficiency: N/A
Efficacy: 83.9 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 72.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P753460

CATALOG NUMBER: LD4D75BD010-EU4DR6070959024-4LBS1B

Luminous Intensity Polar Plot





TEST NUMBER: P753460

CATALOG NUMBER: LD4D75BD010-EU4DR6070959024-4LBS1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	108	106	111	109	106	104	105	103	101		101	99	98		97
2	108	103	99	96	106	101	98	95	98	95	92		95	93	90		92
3	102	96	91	87	100	95	90	86	92	88	85		90	86	84		87
4	97	90	84	80	95	88	83	79	86	82	78		84	81	78		82
5	92	84	78	74	91	83	77	73	81	76	73		79	75	72		78
6	87	79	73	68	86	78	72	68	76	71	68		75	70	67		74
7	83	74	68	63	82	73	67	63	72	67	63		71	66	63		69
8	79	69	63	59	78	69	63	59	68	63	59		67	62	59		66
9	75	65	59	55	74	65	59	55	64	59	55		63	58	55		62
10	72	62	56	52	71	61	56	52	61	55	52		60	55	52		59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	664426
5°	662796
10°	684816
15°	685522
20°	630757
25°	536498
30°	408795
35°	289080
40°	169758
45°	68498
50°	22862
55°	11010
60°	4523
65°	672
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 68498 cd/sqm



TEST NUMBER: P753460

CATALOG NUMBER: LD4D75BD010-EU4DR6070959024-4LBS1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	583.0	9.6
10°-20°	1678.9	27.6
20°-30°	2009.5	33.1
30°-40°	1344.0	22.1
40°-50°	398.5	6.6
50°-60°	57.3	0.9
60°-70°	5.5	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4271.4	70.3
0°-40°	5615.4	92.4
0°-60°	6071.1	99.9
0°-90°	6076.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6076.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6081	
5°	6043	583
15°	6060	1679
25°	4450	2009
35°	2167	1344
45°	443	398
55°	58	57
65°	3	5
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P753460

CATALOG NUMBER: LD4D75BD010-EU4DR6070959024-4LBS1B

CANDELA DISTRIBUTION (FULL):

0°	
0°	6081.1
2.5°	6073.3
5°	6043.1
7.5°	6125.1
10°	6172.5
12.5°	6163.9
15°	6060.4
17.5°	5816.3
20°	5424.8
22.5°	4954.7
25°	4450.2
27.5°	3881.9
30°	3240.2
32.5°	2667.5
35°	2167.3
37.5°	1666.2
40°	1190.2
42.5°	784.8
45°	443.3
47.5°	226.8
50°	134.5
52.5°	87.1
55°	57.8
57.5°	37.1
60°	20.7
62.5°	8.6
65°	2.6
67.5°	0.9
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)