

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P750376

Luminaire Tested: LD4D55D010-EU4DR6055659035-4LBDP1H

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P750376
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D55D010-EU4DR6055659035-4LBDP1H
Description: 4 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5544.8 lumens
Efficiency: N/A
Efficacy: 95.3 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 58.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P750376
CATALOG NUMBER: LD4D55D010-EU4DR6055659035-4LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P750376

CATALOG NUMBER: LD4D55D010-EU4DR6055659035-4LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93																			
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86																			
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80																			
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70																			
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66																			
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62																			
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59																			
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55																			
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	719504
5°	737190
10°	746103
15°	710758
20°	626676
25°	506865
30°	342849
35°	171810
40°	27870
45°	27272
50°	27826
55°	28250
60°	29020
65°	29680
70°	30380
75°	30733
80°	29636
85°	24696

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 30733 cd/sqm



TEST NUMBER: P750376

CATALOG NUMBER: LD4D55D010-EU4DR6055659035-4LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	642.4	11.6
10°-20°	1738.1	31.3
20°-30°	1870.0	33.7
30°-40°	812.9	14.7
40°-50°	136.5	2.5
50°-60°	132.8	2.4
60°-70°	113.5	2.0
70°-80°	76.0	1.4
80°-90°	22.7	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4250.5	76.7
0°-40°	5063.3	91.3
0°-60°	5332.6	96.2
0°-90°	5544.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5544.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6585	
5°	6721	642
15°	6284	1738
25°	4204	1870
35°	1288	813
45°	176	137
55°	148	133
65°	115	114
75°	73	76
85°	20	23
90°	0	



TEST NUMBER: P750376

CATALOG NUMBER: LD4D55D010-EU4DR6055659035-4LBDP1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	6585.2
2.5°	6770.3
5°	6721.4
7.5°	6736.9
10°	6724.9
12.5°	6586.0
15°	6283.5
17.5°	5877.3
20°	5389.7
22.5°	4867.8
25°	4204.4
27.5°	3362.9
30°	2717.5
32.5°	2094.5
35°	1288.1
37.5°	551.1
40°	195.4
42.5°	180.0
45°	176.5
47.5°	170.5
50°	163.7
52.5°	156.0
55°	148.3
57.5°	140.5
60°	132.8
62.5°	124.3
65°	114.8
67.5°	105.4
70°	95.1
72.5°	84.0
75°	72.8
77.5°	60.0
80°	47.1
82.5°	33.4
85°	19.7
87.5°	6.9
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)