

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P750454

Luminaire Tested: LD4D55D010-EU4DR6555659035-4LBDP1H

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P750454
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D55D010-EU4DR6555659035-4LBDP1H
Description: 4 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4844.9 lumens
Efficiency: N/A
Efficacy: 83.2 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 58.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P750454

CATALOG NUMBER: LD4D55D010-EU4DR6555659035-4LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P750454
 CATALOG NUMBER: LD4D55D010-EU4DR6555659035-4LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93			
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87			
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80			
4	97	89	84	79	95	88	83	79	86	82	78	84	80	77	82	79	76	75			
5	92	83	78	73	90	83	77	73	81	76	72	79	75	72	77	74	71	69			
6	87	78	72	68	86	77	72	68	76	71	67	74	70	67	73	69	66	65			
7	83	73	67	63	81	73	67	63	71	66	62	70	66	62	69	65	62	60			
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	57			
9	75	65	59	55	74	65	59	55	64	58	55	63	58	55	62	58	54	53			
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	521185
5°	521618
10°	539987
15°	540882
20°	497973
25°	424297
30°	324808
35°	229472
40°	135456
45°	54993
50°	19939
55°	11106
60°	6359
65°	3516
70°	3674
75°	2871
80°	2957
85°	2507

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 54993 cd/sqm



TEST NUMBER: P750454

CATALOG NUMBER: LD4D55D010-EU4DR6555659035-4LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	459.3	9.5
10°-20°	1324.9	27.3
20°-30°	1589.7	32.8
30°-40°	1068.3	22.1
40°-50°	319.8	6.6
50°-60°	56.4	1.2
60°-70°	16.1	0.3
70°-80°	7.9	0.2
80°-90°	2.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3374.0	69.6
0°-40°	4442.3	91.7
0°-60°	4818.5	99.5
0°-90°	4844.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4844.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4770	
5°	4756	459
15°	4782	1325
25°	3520	1590
35°	1720	1068
45°	356	320
55°	58	56
65°	14	16
75°	7	8
85°	2	2
90°	0	



TEST NUMBER: P750454

CATALOG NUMBER: LD4D55D010-EU4DR6555659035-4LBDP1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	4770.1
2.5°	4790.5
5°	4755.9
7.5°	4827.8
10°	4867.1
12.5°	4857.6
15°	4781.7
17.5°	4595.9
20°	4282.8
22.5°	3914.0
25°	3519.5
27.5°	3074.1
30°	2574.5
32.5°	2121.7
35°	1720.4
37.5°	1323.9
40°	949.7
42.5°	620.2
45°	355.9
47.5°	188.4
50°	117.3
52.5°	81.3
55°	58.3
57.5°	42.0
60°	29.1
62.5°	19.0
65°	13.6
67.5°	12.2
70°	11.5
72.5°	8.8
75°	6.8
77.5°	6.1
80°	4.7
82.5°	3.4
85°	2.0
87.5°	1.4
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)