

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P750001

Luminaire Tested: LD4D55D010-EU4DR3555659040-4LBDP1MW

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P750001
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-20)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D55D010-EU4DR3555659040-4LBDP1MW
Description: 4 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 35° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5183.9 lumens
Efficiency: N/A
Efficacy: 89.1 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.54
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 58.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P750001
CATALOG NUMBER: LD4D55D010-EU4DR3555659040-4LBDP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P750001

CATALOG NUMBER: LD4D55D010-EU4DR3555659040-4LBDP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																								
RCR																																																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																																				
1	115	112	110	108	112	110	108	107	106	105	103	103	101	100	99	98	98	96																																				
2	110	106	103	101	108	105	102	99	102	99	97	99	97	95	96	95	93	92																																				
3	106	101	97	94	105	100	96	93	97	95	92	95	93	91	93	91	89	88																																				
4	103	97	92	89	101	96	92	89	94	90	88	92	89	87	90	88	86	84																																				
5	99	93	88	85	98	92	87	84	90	86	84	89	85	83	87	84	82	81																																				
6	96	89	84	81	94	88	84	81	87	83	80	85	82	80	84	81	79	78																																				
7	93	85	81	78	91	85	80	77	84	80	77	83	79	77	82	79	76	75																																				
8	90	82	78	74	88	82	77	74	81	77	74	80	76	74	79	76	73	72																																				
9	87	79	75	72	86	79	75	72	78	74	71	77	74	71	77	73	71	70																																				
10	84	77	72	69	83	76	72	69	76	72	69	75	71	69	74	71	69	68																																				

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1558441
5°	1521817
10°	1371562
15°	1064548
20°	603793
25°	234903
30°	87633
35°	48031
40°	31393
45°	19114
50°	12171
55°	8591
60°	6293
65°	3413
70°	256
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 19114 cd/sqm



TEST NUMBER: P750001

CATALOG NUMBER: LD4D55D010-EU4DR3555659040-4LBDP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1276.1	24.6
10°-20°	2491.5	48.1
20°-30°	1016.1	19.6
30°-40°	243.2	4.7
40°-50°	101.4	2.0
50°-60°	42.0	0.8
60°-70°	13.1	0.3
70°-80°	0.3	0.0
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4783.8	92.3
0°-40°	5027.0	97.0
0°-60°	5170.3	99.7
0°-90°	5183.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5183.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	14264	
5°	13875	###
15°	9411	2492
25°	1948	1016
35°	360	243
45°	124	101
55°	45	42
65°	13	13
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P750001

CATALOG NUMBER: LD4D55D010-EU4DR3555659040-4LBDP1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	14263.5
2.5°	14177.9
5°	13875.3
7.5°	13271.7
10°	12362.4
12.5°	11082.1
15°	9411.2
17.5°	7367.8
20°	5192.9
22.5°	3311.3
25°	1948.5
27.5°	1101.4
30°	694.6
32.5°	487.7
35°	360.1
37.5°	278.5
40°	220.1
42.5°	169.6
45°	123.7
47.5°	92.6
50°	71.6
52.5°	56.8
55°	45.1
57.5°	36.6
60°	28.8
62.5°	21.0
65°	13.2
67.5°	4.7
70°	0.8
72.5°	0.8
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.8
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)