

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P750467

Luminaire Tested: LD4D55D010-EU4DR6555659040-4LBDP1H

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P750467
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D55D010-EU4DR6555659040-4LBDP1H
Description: 4 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5071.4 lumens
Efficiency: N/A
Efficacy: 87.1 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 58.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P750467
CATALOG NUMBER: LD4D55D010-EU4DR6555659040-4LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P750467

CATALOG NUMBER: LD4D55D010-EU4DR6555659040-4LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93																			
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87																			
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80																			
4	97	89	84	79	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	83	78	73	90	83	77	73	81	76	72	79	75	72	77	74	71	69																			
6	87	78	72	68	86	77	72	68	76	71	67	74	70	67	73	69	66	65																			
7	83	73	67	63	81	73	67	63	71	66	62	70	66	62	69	65	62	60																			
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	57																			
9	75	65	59	55	74	65	59	55	64	58	55	63	58	55	62	58	54	53																			
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	545561
5°	546011
10°	565227
15°	566163
20°	521251
25°	444128
30°	339998
35°	240209
40°	141788
45°	57558
50°	20873
55°	11620
60°	6665
65°	3671
70°	3865
75°	2997
80°	3146
85°	2633

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 57558 cd/sqm



TEST NUMBER: P750467

CATALOG NUMBER: LD4D55D010-EU4DR6555659040-4LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	480.8	9.5
10°-20°	1386.9	27.3
20°-30°	1664.0	32.8
30°-40°	1118.3	22.1
40°-50°	334.8	6.6
50°-60°	59.1	1.2
60°-70°	16.8	0.3
70°-80°	8.2	0.2
80°-90°	2.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3531.7	69.6
0°-40°	4649.9	91.7
0°-60°	5043.8	99.5
0°-90°	5071.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5071.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4993	
5°	4978	481
15°	5005	1387
25°	3684	1664
35°	1801	1118
45°	372	335
55°	61	59
65°	14	17
75°	7	8
85°	2	3
90°	0	



TEST NUMBER: P750467

CATALOG NUMBER: LD4D55D010-EU4DR6555659040-4LBDP1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	4993.2
2.5°	5014.4
5°	4978.3
7.5°	5053.5
10°	5094.6
12.5°	5084.7
15°	5005.2
17.5°	4810.8
20°	4483.0
22.5°	4097.0
25°	3684.0
27.5°	3217.8
30°	2694.9
32.5°	2220.9
35°	1800.9
37.5°	1385.8
40°	994.1
42.5°	649.2
45°	372.5
47.5°	197.3
50°	122.8
52.5°	85.1
55°	61.0
57.5°	44.0
60°	30.5
62.5°	19.9
65°	14.2
67.5°	12.8
70°	12.1
72.5°	9.2
75°	7.1
77.5°	6.4
80°	5.0
82.5°	3.5
85°	2.1
87.5°	1.4
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)