

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P750014

Luminaire Tested: LD4D55D010-EU4DR3555659050-4LBDP1MW

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P750014
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-20)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D55D010-EU4DR3555659050-4LBDP1MW
Description: 4 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 35° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5221.0 lumens
Efficiency: N/A
Efficacy: 89.7 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.54
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 58.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P750014

CATALOG NUMBER: LD4D55D010-EU4DR3555659050-4LBDP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P750014

CATALOG NUMBER: LD4D55D010-EU4DR3555659050-4LBDP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	115	112	110	108	112	110	108	107	106	105	103	103	101	100	99	98	98	96		
2	110	106	103	101	108	105	102	99	102	99	97	99	97	95	96	95	93	92		
3	106	101	97	94	105	100	96	93	97	95	92	95	93	91	93	91	89	88		
4	103	97	92	89	101	96	92	89	94	90	88	92	89	87	90	88	86	84		
5	99	93	88	85	98	92	87	84	90	86	84	89	85	83	87	84	82	81		
6	96	89	84	81	94	88	84	81	87	83	80	85	82	80	84	81	79	78		
7	93	85	81	78	91	85	80	77	84	80	77	83	79	77	82	79	76	75		
8	90	82	78	74	88	82	77	74	81	77	74	80	76	74	79	76	73	72		
9	87	79	75	72	86	79	75	72	78	74	71	77	74	71	77	73	71	70		
10	84	77	72	69	83	76	72	69	76	72	69	75	71	69	74	71	69	68		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1569574
5°	1532686
10°	1381359
15°	1072161
20°	608107
25°	236579
30°	88264
35°	48378
40°	31621
45°	19253
50°	12256
55°	8648
60°	6337
65°	3438
70°	256
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 19253 cd/sqm



TEST NUMBER: P750014

CATALOG NUMBER: LD4D55D010-EU4DR3555659050-4LBDP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1285.2	24.6
10°-20°	2509.3	48.1
20°-30°	1023.4	19.6
30°-40°	244.9	4.7
40°-50°	102.1	2.0
50°-60°	42.2	0.8
60°-70°	13.2	0.3
70°-80°	0.3	0.0
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4818.0	92.3
0°-40°	5062.9	97.0
0°-60°	5207.2	99.7
0°-90°	5221.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5221.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	14365	
5°	13974	###
15°	9478	2509
25°	1962	1023
35°	363	245
45°	125	102
55°	45	42
65°	13	13
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P750014

CATALOG NUMBER: LD4D55D010-EU4DR3555659050-4LBDP1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	14365.4
2.5°	14279.2
5°	13974.4
7.5°	13366.5
10°	12450.7
12.5°	11161.2
15°	9478.5
17.5°	7420.4
20°	5230.0
22.5°	3335.0
25°	1962.4
27.5°	1109.3
30°	699.6
32.5°	491.2
35°	362.7
37.5°	280.5
40°	221.7
42.5°	170.8
45°	124.6
47.5°	93.2
50°	72.1
52.5°	57.2
55°	45.4
57.5°	36.8
60°	29.0
62.5°	21.2
65°	13.3
67.5°	4.7
70°	0.8
72.5°	0.8
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.8
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)