

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P750483

Luminaire Tested: LD4D55D010-EU4DR6555659050-4LBS1B

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P750483  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D55D010-EU4DR6555659050-4LBS1B  
Description: 4 INCH ROUND SHALLOW SPECULAR BLACK TRIM, WITH 65° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4991.8 lumens  
Efficiency: N/A  
Efficacy: 85.8 lumens/watt  
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96  
Luminous Opening: Circular (Dia: 0.48' x H: 0')  
CIE Type: Direct


Input Watts (W): 58.2  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



Downlight

TEST NUMBER: P750483  
CATALOG NUMBER: LD4D55D010-EU4DR6555659050-4LBS1B

### Luminous Intensity Polar Plot





TEST NUMBER: P750483  
 CATALOG NUMBER: LD4D55D010-EU4DR6555659050-4LBS1B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10		0		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93			
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85			
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78			
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72			
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66			
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61			
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56			
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52			
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49			
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	264716
5°	264044
10°	263818
15°	255685
20°	232772
25°	202843
30°	168712
35°	133677
40°	96483
45°	60956
50°	31774
55°	16882
60°	8866
65°	4878
70°	2049
75°	2257
80°	1581
85°	1340

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 60956 cd/sqm



TEST NUMBER: P750483

CATALOG NUMBER: LD4D55D010-EU4DR6555659050-4LBS1B

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	428.6	8.6
10°-20°	1173.7	23.5
20°-30°	1434.7	28.7
30°-40°	1164.1	23.3
40°-50°	580.1	11.6
50°-60°	161.8	3.2
60°-70°	36.8	0.7
70°-80°	9.6	0.2
80°-90°	2.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3037.1	60.8
0°-40°	4201.2	84.2
0°-60°	4943.0	99.0
0°-90°	4991.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4991.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4532	
5°	4504	429
15°	4229	1174
25°	3148	1435
35°	1875	1164
45°	738	580
55°	166	162
65°	35	37
75°	10	10
85°	2	2
90°	0	



TEST NUMBER: P750483

CATALOG NUMBER: LD4D55D010-EU4DR6555659050-4LBS1B

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	4532.5
2.5°	4529.1
5°	4503.8
7.5°	4489.2
10°	4448.5
12.5°	4365.9
15°	4228.7
17.5°	4014.3
20°	3745.2
22.5°	3454.8
25°	3147.7
27.5°	2819.4
30°	2501.7
32.5°	2188.0
35°	1874.9
37.5°	1562.5
40°	1265.5
42.5°	987.1
45°	738.0
47.5°	514.2
50°	349.7
52.5°	241.1
55°	165.8
57.5°	111.9
60°	75.9
62.5°	52.6
65°	35.3
67.5°	18.0
70°	12.0
72.5°	11.3
75°	10.0
77.5°	6.7
80°	4.7
82.5°	3.3
85°	2.0
87.5°	1.3
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)