

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P753550

Luminaire Tested: LD4D75BD010-EU4DR6570959027-4LBDP1MW

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P753550
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D75BD010-EU4DR6570959027-4LBDP1MW
Description: 4 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5261.0 lumens
Efficiency: N/A
Efficacy: 72.7 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 72.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P753550

CATALOG NUMBER: LD4D75BD010-EU4DR6570959027-4LBDP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P753550

CATALOG NUMBER: LD4D75BD010-EU4DR6570959027-4LBDP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	111	108	106	111	108	106	104	104	103	101		101	99	98		97
2	108	103	99	95	106	101	97	94	98	95	92		95	92	90		92
3	102	96	91	87	100	94	90	86	92	88	85		89	86	83		87
4	97	89	84	79	95	88	83	79	86	82	78		84	80	77		82
5	92	83	78	73	90	83	77	73	81	76	72		79	75	72		77
6	87	78	72	68	86	77	72	68	76	71	67		74	70	67		73
7	83	73	67	63	81	73	67	63	71	66	62		70	66	62		69
8	79	69	63	59	77	68	63	59	67	62	58		66	62	58		65
9	75	65	59	55	74	65	59	55	64	58	55		63	58	55		62
10	71	61	56	52	70	61	55	52	60	55	51		59	55	51		59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	565949
5°	566422
10°	586362
15°	587327
20°	540739
25°	460728
30°	352703
35°	249186
40°	147094
45°	59706
50°	21638
55°	12058
60°	6927
65°	3800
70°	3993
75°	3124
80°	3272
85°	2758

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 59706 cd/sqm



TEST NUMBER: P753550

CATALOG NUMBER: LD4D75BD010-EU4DR6570959027-4LBDP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	498.8	9.5
10°-20°	1438.7	27.3
20°-30°	1726.2	32.8
30°-40°	1160.1	22.1
40°-50°	347.3	6.6
50°-60°	61.3	1.2
60°-70°	17.4	0.3
70°-80°	8.6	0.2
80°-90°	2.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3663.7	69.6
0°-40°	4823.8	91.7
0°-60°	5232.3	99.5
0°-90°	5261.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5261.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5180	
5°	5164	499
15°	5192	1439
25°	3822	1726
35°	1868	1160
45°	386	347
55°	63	61
65°	15	17
75°	7	9
85°	2	3
90°	0	



TEST NUMBER: P753550

CATALOG NUMBER: LD4D75BD010-EU4DR6570959027-4LBDP1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	5179.8
2.5°	5201.9
5°	5164.4
7.5°	5242.4
10°	5285.1
12.5°	5274.8
15°	5192.3
17.5°	4990.7
20°	4650.6
22.5°	4250.1
25°	3821.7
27.5°	3338.1
30°	2795.6
32.5°	2303.9
35°	1868.2
37.5°	1437.6
40°	1031.3
42.5°	673.5
45°	386.4
47.5°	204.6
50°	127.3
52.5°	88.3
55°	63.3
57.5°	45.6
60°	31.7
62.5°	20.6
65°	14.7
67.5°	13.2
70°	12.5
72.5°	9.6
75°	7.4
77.5°	6.6
80°	5.2
82.5°	3.7
85°	2.2
87.5°	1.5
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)