

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P752015

Luminaire Tested: LD4D65D010-EU4DR6555659035-4LBDP1LI

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P752015
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D65D010-EU4DR6555659035-4LBDP1LI
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6186.9 lumens
Efficiency: N/A
Efficacy: 85.0 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 72.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P752015
CATALOG NUMBER: LD4D65D010-EU4DR6555659035-4LBDP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P752015
 CATALOG NUMBER: LD4D65D010-EU4DR6555659035-4LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93																			
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87																			
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80																			
4	97	89	84	79	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	83	78	73	90	83	77	73	81	76	72	79	75	72	77	74	71	69																			
6	87	78	72	68	86	77	72	68	76	71	67	74	70	67	73	69	66	65																			
7	83	73	67	63	81	73	67	63	71	66	62	70	66	62	69	65	62	60																			
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	57																			
9	75	65	59	55	74	65	59	55	64	58	55	63	58	55	62	58	54	53																			
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	665551
5°	666108
10°	689553
15°	690703
20°	635908
25°	541826
30°	414788
35°	293042
40°	172967
45°	70228
50°	25463
55°	14172
60°	8129
65°	4473
70°	4696
75°	3673
80°	3838
85°	3259

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 70228 cd/sqm



TEST NUMBER: P752015
 CATALOG NUMBER: LD4D65D010-EU4DR6555659035-4LBDP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	586.6	9.5
10°-20°	1691.9	27.3
20°-30°	2030.0	32.8
30°-40°	1364.2	22.1
40°-50°	408.4	6.6
50°-60°	72.1	1.2
60°-70°	20.5	0.3
70°-80°	10.1	0.2
80°-90°	3.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4308.5	69.6
0°-40°	5672.8	91.7
0°-60°	6153.2	99.5
0°-90°	6186.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6186.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6091	
5°	6073	587
15°	6106	1692
25°	4494	2030
35°	2197	1364
45°	454	408
55°	74	72
65°	17	20
75°	9	10
85°	3	3
90°	0	



TEST NUMBER: P752015

CATALOG NUMBER: LD4D65D010-EU4DR6555659035-4LBDP1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	6091.4
2.5°	6117.4
5°	6073.3
7.5°	6165.0
10°	6215.2
12.5°	6203.1
15°	6106.2
17.5°	5869.0
20°	5469.1
22.5°	4998.2
25°	4494.4
27.5°	3925.6
30°	3287.7
32.5°	2709.4
35°	2197.0
37.5°	1690.6
40°	1212.7
42.5°	792.1
45°	454.5
47.5°	240.6
50°	149.8
52.5°	103.9
55°	74.4
57.5°	53.7
60°	37.2
62.5°	24.2
65°	17.3
67.5°	15.6
70°	14.7
72.5°	11.3
75°	8.7
77.5°	7.8
80°	6.1
82.5°	4.3
85°	2.6
87.5°	1.7
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)